

Philips
Multimedia Speaker 5.1



A3.610

Adrenaline for your ears

Home cinema performance, PC versatility

Connect your PC, TV and MP3 player to the A3.610 5.1 channel soft flat panel audio system and enjoy quality home cinema performance from an attractively priced multimedia system.

Your computer never sounded so good

- Enjoy PC audio with the quality of a home audio system
- Over 75 years of audio experience
- Soft flat panel for quality sound from ultra-thin speakers

Experience true multimedia

- Compatible with music, games, film & internet audio sources
- 5.1 channel sound for Dolby Digital® and EAX® reproduction
- Simultaneously connect 3 audio sources to the speakers
- Easy to connect to either a PC or a laptop

Hear every detail

- Subwoofer for deep bass plus satellites for clear highs
- Bass Reflex Speaker System delivers a powerful, deeper bass
- Digital Dynamic Bass Boost for optimized bass at any volume
- Wooden housing for quality bass reproduction

PHILIPS

Highlights

Home audio quality on the PC

Philips has used over 75 years experience at the leading edge of audio to create PC audio products with the same performance as our award-winning home audio systems.

75 Years of audio experience

Philips invented the CD, led the team that wrote the USB audio specification and has produced millions of audio systems, home cinema sets and TV's over many decades. As a leader in audio innovation, you can trust Philips to make PC sound systems of the highest sound quality.

Soft Flat Panel

Soft Flat Panel is an award-winning technology using 3 unique Philips patents that makes it possible to reproduce premium sound quality from ultra-thin speakers.

Music, games, films, internet

All types of music, games, films and internet audio sources can be played, so no matter what you want to hear, we make your multimedia experiences sound more involving than ever.

5.1 channel playback

5.1 channel sound for reproduction of Dolby Digital® and EAX® sound sources

3-Way Audio Input

Connect 3 audio sources (such as TV, PC and MP3 player) to the speaker system at the same time. Switching between the sources can now be done at the touch of a button without having to swap any cables.

For PC or Laptop

Can be connected to either a PC or a laptop

Subwoofer + satellite speakers

The audio system is separated into a subwoofer that is optimized to reproduce bass frequencies and satellite speakers that are optimised for mid- and high-range frequencies. The result is a system that powerfully reproduces the full range of audio frequencies from deep bass to crystal clear high notes with the minimum of distortion.



Bass Reflex Speaker System

Bass Reflex Speaker System delivers a deep bass experience from a compact loudspeaker box system. It differs from a conventional loudspeaker box system in the addition of a bass pipe that is acoustically aligned to the woofer to optimize the low frequency roll-off of the system. The result is deeper controlled bass and lower distortion. The system works by resonating the air mass in the bass pipe to vibrate like a conventional woofer. Combined with the response of the woofer, the system extends the overall low frequency sounds to create a whole new dimension of deep bass.

Digital Dynamic Bass Boost

Digital Dynamic Bass Boost is an intelligent bass booster that delivers maximum bass enhancement at high volumes without sound distortion and at low volumes without compromising on bottom-end bass frequencies. Technologically advanced electronics constantly monitor volume and bass levels, precisely calibrating both to prevent sound distortion, thus producing optimized bass. Digital Dynamic Bass Boost enables the enjoyment of superb bass performance - regardless of the chosen volume level.

Wooden subwoofer

The housing of the subwoofer is made from wood, giving it superior stability and acoustical performance.

Quick set-up

Color-coded cables, clear labelling and easy to understand documentation mean you'll be up and running in minutes

Infra-red remote control

Infra-red remote control provides the most convenient way to control the device without leaving your chair.

Magnetic Shielding

Because the powerful magnets in speaker drivers are magnetically shielded, there's no danger of image distortion or damage when placed close to your PC monitor screen.

Specifications

Sound

- Bass enhancement: Digital Bass Boost
- Output power (RMS): 5 x 20 + 100W
- Sound Enhancement: Balance, EQ by genre
- Music Power: 400 W
- Volume Control: digital
- Wires: Fixed Wires

Loudspeakers

- Loudspeaker Enhancement: Magnetic Shielded LSB
- Satellite speaker freq range: 200-20000Hz Hz
- Subwoofer freq range: 20-200Hz Hz

Connectivity

- Power: Built-in transformer

Convenience

- Power on indication

Accessories

- Included accessories: Quick install guide
- Remote control: 17 Key

Dimensions

- Carton dimensions (WxDxH): 410 x 482 x 293 mm
- Product weight: 9.04 kg



Issue date 2014-02-12

Version: 5.0.6

12 NC: 9306 000 00056
EAN: 87 10101 08080 2

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com