

PHILIPS

Air Purifier

Series 1000i

Reduces allergens, gases, odors

Allergens display

Connected app with allergen advice

Ideal for small to medium rooms



AC1214/40

Intelligent purification

Connect to cleaner air

With professional-grade sensing performance, the Philips Air Purifier Series 1000i automatically monitors, reacts and purifies the air – then gives real-time air quality feedback via the display and connected app. Also use the App for outdoor air quality and allergen management advice. Ideal for bedrooms, with quiet night sense auto-mode.

Superior purification

- Captures 99.97% of particles that pass through the filter
- Reduces allergens, gases, odors

Intelligent purification

- Visualized air quality feedback
- 3 auto modes: General, Allergen, and night sense
- 4 manual settings, including turbo speed
- Automatically monitors, reacts & purifies the air

With Air Quality app

- Control purifier from anywhere
- Track indoor and outdoor air quality
- Allergen management advice

Long-lasting performance

- Ideal for small to medium rooms

Highlights

99.97% filtration



Designed with a multi-stage active filtration system, which captures up to 99.97% of particles that pass through the filter as small as 0.3 microns – the size of most common airborne allergens, particles, bacteria and viruses.

Visualized air quality

In real-time, AeraSense shows you the IAI index via a numerical display and a color ring on the dashboard of the air purifier. The numerical display is an index of the indoor air quality. The color ring provides an additional visual cue, ranging from blue (good air quality) to red (bad air quality).

3 auto modes



The Philips Air Purifier has 3 automatic purification settings: a General mode, an extra-sensitive Allergen mode, and a night sense mode that automatically turns down the lights and fan speed when the room is dark. You can choose your preferred mode to personalize and optimize your purification.

4 manual settings



In addition to the 3 auto modes, the purifier also has 4 manual modes. Choose one of four different speed settings: from the extra-quiet 'Speed 1' to the extra-powerful 'Turbo Speed' mode. Pick one that is ideal for your required purification.

AeraSense technology



AeraSense

Benchmarked against a professional-grade sensor, Philips AeraSense technology is highly effective in sensing even the slightest change in indoor air conditions. It continuously monitors the air and automatically adjusts the fan speed when it detects a change in particles.


Remotely control purifier

Control your air purifier from anywhere with the connected app. Change the fan speed, set a schedule, or see your filter lifetime through the easy-to-use App.

Track your air quality

Use the app to check your indoor and outdoor air quality. The Air Purifier constantly feeds indoor air quality data to the app, which is then combined with outdoor pollution and pollen data to give you a complete picture of your air quality.

Allergen management advice



Based on the indoor and outdoor air quality levels, the app will give you advice to help you with your allergen management regimen.

Ideal for small to medium rooms



The Philips Air Purifier has been designed for small to medium rooms, such as a bedroom. It is recommended for rooms up to 200 sq ft.

Superior purification



With cutting edge sensing and purification technology, the Philips Air Purifier Series 1000 is proven to reduce allergens, odors, and VOCs. The pre-filter and True HEPA filter remove particles. The Active Carbon filter reduces gases and odors.

Specifications

Performance

Room size: 200 sq ft/ 18.85 m²
0.3µm particle removal: 99.97 %
Ultra fine particle removal: 20 nm
Recommended HEPA life time: 12 months
Recommended AC life time: 6 months
Sound Power: 32 - 62 dB(A)

Features

VitaShield IPS
AeraSense technology
Air Quality feedback: Numerical
PM2.5 sensor
Modes: 3 auto modes
Fan speed: 4 manual speed settings

Child lock
Healthy air lock & Alert
Motor: DC

Design and finishing

Color(s): White
Color of control panel: Black 7C
Control panel type: Touch Panel
Material of main body: ABS

Technical specifications

Voltage: 120 V
Frequency: 50/60 Hz
Cord length: 1.8 m

Weight and dimensions

Weight of product: 183.78Oz/5.21 kg
Weight incl. packaging: 234.22Oz/6.64 kg
Dimension of product (LxWxH):
8.27x12.80x21.38 inch/ 210 x 325 x 543
Dimension of packaging (LxWxH):
10.12x14.61x23.74 inch / 257x371x603 mm

Country of origin

Made in: China

Sustainability

Packaging: > 90% recycled materials
User manual: 100% recycled paper

Service

2-year guarantee

