

PHILIPS

Air purifier

Sleep mode

AC4025/10



A healthier sleep, always

Purifier with dedicated Sleep mode

Breathe healthy air with the Philips air purifier. Its advanced filtration system filters out bacteria, allergens and harmful agents. The Healthy air protect alert assures you of healthy air always.

Healthy Air

- With advanced filtration system
- Sleep mode cleans silently with dimmed indicators

Always

- Healthy air protect alert warns you when to replace filter

Simplicity

- 3-step fan speed lets you adjust air flow to your liking
- 1/4/8 hours easy-to-set timer

Highlights

Advanced filtration system

The advanced filtration system eliminates harmful agents in two stages: In stage 1, the activated carbon filter acts as pre-filter to catch big particles like human hair and regular house dust, and effectively removes odors and harmful gases. In stage 2, the HEPA filter filters out fine dust, bacteria and allergens.

Sleep mode



This Philips purifier operates very quietly and dimmed lights, to allow you to sleep undisturbed. The purifier switches to lower activity level, the fan speed and noise level are reduced and the energy consumption is minimised.

Healthy air protect alert



Healthy air protect alert gives you a timely warning when to replace the filter. When the filter is not replaced in time, the appliance stops functioning to avoid running with no effect since filter is full. It is your assurance of healthy air always.

3-step fan speed



3-step fan speed lets you adjust air flow to your liking.

1/4/8 hours easy-to-set timer

Appliance operates for a set number of hours and automatically switches off when set time has elapsed.

Specifications

Design specifications

Front cover: white

Materials of main body: ABS plastic

Rim: green

Logistic data

12NC code: 883402510280 (India)

883402510640 (Thailand)

EAN F-box: 8710103701170 (India) -

8710103678953 (Thailand)

Country of origin: China

Weight and dimensions

Product weight: 4.5 kg

F-box weight (incl. product): 6.1 kg

Product dimensions (W x D x H): 333 x 186 x 510 mm

F-box dimensions (W x D x H): 421 x 273 x 605 mm

Interactivity

Frequency: 50 Hz

Voltage: 220-240 V

Wattage: 40 W

Cord length: 1.8 m

Noise level: 36 (Sleep) - 54 (Highest speed) dB

Performance

CADR (cigarette smoke): 147 m³/h**

Filters out PM2.5: >99% ***

Filters out bacteria: >99.9% ****

Replacement

AC filter: AC4103

HEPA filter: AC4104



** Tested by Shanghai Institute of Measurement and Testing Technology (SIMT) in 30m³ chamber according to GB/T18801-2008, cigarette smoke used as the particle pollutants

*** Tested by SIMT in 30m³ chamber according to GB/T18801-2008 and GB/T18883-2002, inhalable particles of size smaller than 2.5µm as particles pollutants sampled in mass concentration, initial concentration 5.0±0.5mg/m³, testing time 1hr

**** Tested by Shanghai Institute of Measurement and Testing Technology (SIMT) in 30m³ chamber according to GB21551.3-2010, (Staphylococcus albsp) 8032 as testing bacteria