


PHILIPS

Air Purifier

CADR 341 m³/h

PM2.5 removal rate >99%



AC4372



Healthy air always

With healthy air protect lock

VitaShield IPS professional filtration system effectively filters out harmful gases (formaldehyde, toluene and TVOC etc.) and pollutants (ultrafine particles, allergens, bacteria and viruses) with a size of >0.02 micron. *

Always

- Child lock prevents unintended changes in settings
- Healthy air protect alert/lock
- Smart sensor measures and controls the indoor air quality

Healthy Air

- Turbo mode cleans air instantly at the highest speed
- Smart sensor gives clear feedback on indoor air quality
- VitaShield IPS professional filtration system

Simplicity

- Auto mode ensures hassle-free functioning.
- 1/4/8 hour easy-to-set timer
- 4-step LED indicators show air quality level clearly
- 6 settings in fan speed
- Light sensor automatically turns off all lights at night
- Lower speed & noise level in Silent mode with all lights off

Highlights

VitaShield IPS

VitaShield IPS professional filtration system

Smart sensor

Smart sensor gives clear feedback on indoor air quality.

Healthy air

Healthy air protect alert gives you a timely warning when to replace the filter. When the filter is not replaced in time, the appliance stops functioning to avoid running with no effect wince filter is full. It is your assurance of healthy air always.

Turbo mode

Turbo mode cleans air instantly at the highest speed.

Smart sensor

Smart sensor measures and controls the indoor air quality

Child lock

Child lock prevents unintended changes in settings.

4-step LED indicators

4-step LED indicators show air quality level clearly

Light Sensor

Light sensor automatically turns off all lights at night

Auto mode

Auto mode ensures hassle-free functioning.

Silent mode

Product turns down fan speed and noise level in silent mode, all lights on products are off.

6 settings in fan speed

6 settings to give you ample choice in fan speed.

Timer

1/4/8 hour easy-to-set timer

Specifications

Performance

Filters out TVOCs: 84% **

CADR (cigarette smoke): 341 m³/h**

Filters out PM2.5: 99%**

Filters out toluene: 81%**

Filters out viruses: 99.9% ***

Filters out bacteria: 99.9% **

Filters out formaldehyde**: 90 %

Technical specifications

Voltage: 220-240 V

Frequency: 50 Hz

Cord length: 2.0 m

Air quality sensor(s): Particle

Wattage: 63 W

Noise level: 38 dB(A)

Design specifications

Control panel: Mirror coating touch panel

Fan speed indicators: On control panel

Materials of main body: ABS plastic

Color(s): Glossy white/Golden sparkle

Logistic data

Country of origin: Korea

Replacement

AC filter: AC4153

HEPA filter: AC4154

Multi-care filter: AC4151

Weight and dimensions

Product weight: 7.45 kg

F-box weight (incl. product): 10.14 kg

F-box dimensions (W x D x H): 444 x 305 x 815 mm



** CADR (Cigarette) tested by third party *PM2.5 tested by third party (5.0 +/- 0.5)mg/m³ **Formaldehyde, Toluene, TVOC tested by third party in 30M3 lab in 3 hours **Anti-bacterial properties tested according to GB21551.3 using Staphylococcus Albus, initial concentration is 1*10⁵ cfu/m³

*** Tested for MS2 virus species removal at Intertek Institute, USA ((tested 2hrs in 11 m³ chamber), initial concentration is 1.3*10⁷ pfu/ml

* According to 2008 Microbiological Risk Assessment Report of the World Health Organization (WHO), the avian influenza, human influenza viruses, Legionella, Hepatitis viruses and SARS coronavirus are larger than 0.02 micron.