

PHILIPS

Dispenser

Bottom loading

Hot, cold and ambient water

UV

ADD4970GY



Bottled water redefined

UV kills 99.9% bacteria in the cold water tank*

This floor-standing bottled water dispenser comes with a UV-LED disinfection function which eliminates up to 99.9% of bacteria in the cold water tank* to ensure the cleanness of water.

Cleaner water

- UV-LED kills 99.9% bacteria in the cold water tank**

Thoughtful design for your convenience

- Dual heating powers for your selection
- Compressor cools water efficiently
- Wide dispensing area fits various sizes of containers
- Z-shape 304 stainless steel water pipe

Safeness assured

- Child lock to prevent hot water burns

Highlights

Child lock for hot water

Child lock for hot water keeps children safe from accidental hot water burns.

Compressor cooling

Compressor cooling produces cool water more efficiently and faster, compared to conventional thermoelectric cooling.

Dual heating powers

Dual powers for your selection - 350W high power for fast boil, and 170W low power to save energy.

UV disinfection

Since there's no chlorine, bacteria tend to grow in the water that sits inside the bottle or the cold water tank. Therefore we have the

advanced UV-LED light technology installed in the cold water tank which kills up to 99.9% bacteria**. The UV-LED light activates for 1 hour once the dispenser is connected with power, and works for 1 hour for every 2 hours to make sure the water stay clean.

Wide water dispensing area

Wide dispensing area easily fits various sizes of cup, glass, bowl and even pot.

Z-shape water pipe

The 304 stainless steel water pipe is anti-rust, and the Z-shape helps to reach the bottom of the bottle so that there's no remaining water.

Specifications

General specifications

Cold water temperature: 10 °C

Hot water temperature: 90 °C

Voltage and frequency: 220V~ / 50Hz

Power

Cooling: 85W

Heating: 170W/350W

Country of origin

Water dispenser: China

