



Philips ADR800
Car driving video recorder

Full-HD 1080p
Collision detection
Improved night visibility



ADR80BLX1

Your reliable eye-witness

with collision detection & improved night view

Enjoy driving, Philips automotive driving recorder will protect you in case the unexpected happens. Rely on smart automatic functions, and excellent video performance to provide you with crystal clear evidence in any situation.

Hassle free & reliable with emergency support

- Automatic recording
- No hindering

Impartial evidence anytime

- Collision detection and emergency recording
- Instant replay with proof stamped evidence

Crystal clear images in all driving conditions

- Crystal clear images in all driving conditions

Original equipment quality

- High vibration and temperature resistant

PHILIPS

Highlights

Hassle free & reliable




As soon as you power on your vehicle, the driving recorder starts operating automatically.

Emergency support



In case of a collision, an emergency recording is automatically saved to secure the evidence and prevent overwriting.

Crystal clear images




Capture unseen details with Full-HD quality (1080p) and Night View technology for improved night visibility

Hassle free & easy operation



Screen can switch off automatically, no hindering at night

Impartial evidence anytime



Instant replay to clarify responsibility on the spot, with proof stamped evidence, to support & speed up the insurance claim process

Original equipment quality



High vibration and temperature resistant

Specifications

Product description

- Designation: ADR800
- Technology: Automotive Driving Recorder
- Languages: English, Chinese, Japanese and more
- Interface: Mini USB 2.0, HDMI, micro SD Slot, Microphone, Speaker
- Operating Temperature: 0 ~ 65 °C
- Storage Temperature: -20 ~ 70 °C
- File Format: .MOV AVC audio compression /H.264 video compression
- Fixed Lens: Wide angle lens, FOV 107 (Diagonal)
- Internal Memory: 64Mb SPI Flash
- Random Access Memory: 64Mx16bit (1Gbits) DDR2 SDRAM
- Recording media: Micro SD card (class 4 or higher, up to 32GB)
- Recording Time: 200min @16GB for full HD
- Display: 2" LCD 480*234 dot
- G-sensor
- Auto exposure
- Auto white balance
- Improved night visibility
- LCD Auto Off
- Seamless loop recording
- Automatic recording
- Collision detection & emergency
- Aperture Range: F/#2.2
- Video resolution: Full HD(1920x1080p) @30fps, HD Premium(1280x720)@30fps

Accessories included

- Accessories: Mini USB Car Charger, 3M Mount Bracket, Quick Guide
- Power cable length: 4 m
- Power: 2-24V car adapter

Weight and dimensions

- Box dimensions (L x W x H): 155 x 140 x 90 mm
- Box weight: 355 g
- Product dimensions (L x W x H): 72.8x 53.3x 31.34 mm
- Product weight: 60 g



Issue date 2018-03-20

Version: 6.0.1

12 NC: 8670 001 17503

© 2018 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com