

Portable radio

AE 1000

Free-powered radio

- **AM/FM radio with built-in high efficiency power generator**
Provides the ultimate in functional portability; no worry about the availability of batteries
- **Require no batteries or external power source for operation**
Ideal for use on camping trips and other situations where conventional power sources are not available.
- **Turning the power generator for 1 minute of charging equals 30 minutes of listening**
Maximum charge of 1 hour equals 15 hours of continuous use.
- **Charging LED indicates maximum charge rate**
Provides a visible indication of optimum charge rate for the most efficient use of the built-in charging system.
- **Carrying strap**
- **Rugged design**
- **Dial light**
- **Can also be operated using back up batteries (optional)**



FREE POWER



Let's make things better.



PHILIPS

Standard product information**Tuner**

- Analogue tuning
- Wavebands
 - /00, /01, /11 : FM/MW
 - /04, /14 : FM/LW
 - /17 : FM/AM
- Frequency ranges
 - /00, /01, /11 : FM 87.5 - 108 MHz
 - /00, /01, /11 : MW 525 - 1606.5 kHz
 - /04, /14 : FM 87.5 - 108 MHz
 - /04, /14 : LW 150 - 258 kHz
 - /17 : FM 87.5 - 108 MHz
 - /17 : AM 530 - 1710 kHz
- Ferroceptor for MW and LW
- Telescopic aerial for FM

Amplifier

- Max. output power : 100 mW RMS

Sound system

- Loud speaker : 55 mm

Power supply

- Built-in power generator (2 x 1.5 V Nickel-metal Hydride NiMH batteries included)
- Alternative batteries supply : 2 x 1.5V, type AA/R6/UM3 cell

General

- Material : Polystyrene
- Weight : 350g (excluding batteries)
- Dimensions : 90 mm W x 152 mm H x 60 mm D
- Quantity/ mastercarton : 6

Product highlights

- **AM/FM radio with built-in high efficiency power generator**
Provides the ultimate in functional portability; no worry about the availability of batteries
- **No batteries or external power source required for operation**
Ideal for use on camping trips and other situations where conventional power sources are not available.
- **Tuning the power generator for 1 minute of charging equals 30 minutes of listening**
Maximum charge of 1 hour equals 15 hours of continuous use.
- **LED indicates maximum charge rate**
Provides a visible indication of optimum charge rate for the most efficient use of the built-in charging system.
- **Rugged design**
- **Carrying strap**