

Portable radio

AE 1505

Portable radio

- **Pocket-size for portable use**

Combines high performance with portable convenience wherever you go.

- **AM/FM tuner**

Gives you a wide selection of radio stations to choose from.

- **Built-in speaker**

Provides impressive sound reproduction across a wide frequency range.

- **Loud, good quality sound**

- **Headphone socket**

- **Rotary Handle**

- **Thumbwheel volume control with On/Off switch**

- **Telescopic FM Antenna**

- **Ferroreceptor AM Antenna**



Let's make things better.



PHILIPS

Standard product information**Tuner**

- Analogue tuning
- Wave ranges
 - /00, /01, /11 : FM/MW
 - /14, /04 : FM/LW
 - /17 : FM/AM
 - /00, /01, /11, /17 : FM 87.5 - 108 MHz
 - /00, /01, /11 : MW 525 - 1606.5 kHz
 - /14, /04 : FM 87.5 - 108 MHz
 - /14, /04 : LW 150 - 285 kHz
 - /17 : AM 530 - 1710 kHz
- Telescopic MW and LW
- Telescopic aerial for FM

Amplifier

- Max. output power : 200mW RMS

Sound system

- Loud speaker : 60 mm

Power supply

- Batteries : 2 x 1.5V, type AA/R6/UM3 cell

Connections

- Headphone socket : 3.5mm

General

- Material : polystyrene
- Weight : 180 g excluding batteries
- Dimensions : 76 mm W x 123 mm H x 35 mm D
- Quantity/ dealercarton : 6
- Quantity/ mastercarton : 12

Product highlights

- **Headphone Jack**
Enable headphones to be used for private listening pleasure, without disturbing others.
- **Telescopic FM Antenna**
Extendible FM antenna for excellent FM reception.
- **Ferroceptor AM Antenna**
Built-in ferrite bar antenna for excellent AM reception.
- **Rotary handle**
Handle that provides convenient portability and which
- **Loud Quality Sound**
Folds neatly away when not in use.
- **Thumbwheel Volume Control with On/Off Switch**