

Portable radio

AE 1506

Pocket radio

Compact and complete

- Fully pocketable size
- MW/FM tuner
- Headphone socket

Easy-to-use

- Direct rotary tuning
- Carry handle
- Thumbwheel volume control

Loud, quality sound

- Built-in full-range speaker



PHILIPS

Portable radio



Standard product information

Tuner

- Analogue tuning
- Wavebands
 - FM/MW
 - FM 87.5 - 108 MHz
 - MW 148 - 283.5 kHz
 - LW 525 - 1606.5 kHz

Sound system

- Loud speaker 60 mm
- Max output power (RMS) 200 mW

Power supply

- Batteries 2 x 1.5V, type AA/R6/UM3/cell

Connections

- Headphone socket 3.5mm

General

- Material Polystyrene
- Weight (g) 180
excluding batteries
- Dimensions (mm) 76 W x 123 H
x 35 D
- Quantity/dealer carton 6
- Quantity/master carton 12

Fully pocketable size

MW/FM tuner

Telescopic aerial for FM & Ferroceptor for MW

Headphone socket

Direct rotary tuning

Carry handle

Thumbwheel volume control

Rotary power On/Off and volume Control

Built-in full-range speaker

Printed in Hong Kong 2003-03-24
Specifications subject to modification
without notice
2003 © Koninklijke Philips Electronics N.V.
All rights reserved

www.philips.com
www.audio.philips.com

