



Philips
Portable Radio

FM/MW, Analogue tuning

Built-in speaker
Headphone jack
Battery operated

AE1530

Fully pocketable size

You can enjoy loud, good quality sound wherever you go with this stylish, pocket-size Philips MW/FM pocket radio.

Enjoy your favorite stations

- FM/MW tuner for radio enjoyment

Easy to use

- Single thumbwheel control for volume and on/off switch
- Built-in speaker to enjoy radio out-loud in good sound
- Stereo headphone jack for better personal music enjoyment

PHILIPS

Specifications

Sound

- Sound system: mono
- Volume control: rotary (analogue)
- Output power: 100 mW RMS

Tuner/Reception/Transmission

- Tuner bands: FM, MW

Connectivity

- Audio/Video output: Headphone (3.5mm)

Dimensions

- Product weight: 0.08 kg
- Main unit depth: 19 mm
- Main unit height: 117 mm
- Main unit width: 56 mm

Power

- Battery type: AAA size (LR3)
- Battery voltage: 1.5 V
- Number of batteries: 2



Issue date 2022-04-29

Version: 2.0.17

12 NC: 8670 000 37428
EAN: 87 12581 39894 1

© 2022 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com