

PORTABLE RADIO



PORTABLE RADIO

Basic Specification

- Reception of AM and FM stations
- Telescopic and ferroceptor aerials
- Thumbwheel volume control with on-off switch
- Loud, good quality sound
- Built-in speaker
- Earphone connection
- Rotary handle

Let's make things better.



PHILIPS

TUNER

- Analog tuning
- Wave ranges
 - /00, /01, /11 : FM 87.5 - 108 MHz
 - MW 525 - 1606.5 kHz
 - /04 : FM 87.5 - 108 MHz
 - LW 150 - 285 kHz
- Ferroceptor for MW and LW
- Telescopic aerial for FM

AMPLIFIER

- Max. output power : 120 mW RMS

SPEAKER SYSTEM

- Loud speaker : 60 mm

POWER SUPPLY

- Batteries : 2 x 1.5V, type AA/R6/UM3 cell

CONNECTIONS

- Headphone socket : 3.5 mm

GENERAL

- Material : Polystyrene
- Weight : 200 g (excluding batteries)
- Dimensions : 71 mmW x 120 mmH x 30mmD
- Displaybox dimensions : 80 mmW x 132 mmH x 44 mmD
- Quantity /dealercarton : 6
- Quantity /mastercarton : 12

3122 321 7305 2

Subject to modification without notice

**PHILIPS**