

Portable radio



Pocket size *for portable use*

- AM/FM tuner
- Built-in speaker
- Loud, good quality sound
- Fold-down handle
- Headphone socket
- Telescopic FM antenna
- Ferroreceptor AM antenna
- Thumbwheel volume control with on/off switch



Let's make things better.



PHILIPS

Portable radio



Standard product information

Tuner

- Analogue tuning
- Wavebands
 - /00, /14 FM/MW
 - /04 FM/LW
- Wave ranges
 - FM 87.5 - 108 MHz
 - MW 525 - 1606.5 kHz
 - LW 150 - 285 kHz
- Ferroceptor for MW and LW
- Telescopic aerial for FM

Amplifier

- Max. output power 200mW RMS

Sound system

- Loud speaker 60 mm
- Metal grill

Power supply

- Batteries 2 x 1.5V, type AA/R6/UM3 cell

Connections

- Headphone socket 3.5mm

General

- Material polystyrene
- Weight 210 g (excluding batteries)
- Dimensions (mm) 155 W x 82 H x 38 D
- Quantity/dealercarton 6
- Quantity/mastercarton 12

Pocket size for portable use

Combines high performance with portable convenience wherever you go.

AM/FM tuner

Gives you a wide selection of radio stations to choose from.

Built-in speaker

Provides impressive sound reproduction across a wide frequency range.

Loud, good quality sound

Fold-down handle

Headphone socket

Telescopic FM antenna

Ferroceptor AM antenna

Thumbwheel volume control with on/off switch

Printed in Hong Kong 2000-12-01
Specifications subject to modification without notice
© 2000 Koninklijke Philips Electronics N.V.
All rights reserved

<http://www.philips.com>

Let's make things better.



PHILIPS