

Portable radio

AE 2160

300 hours battery life

- *Mains or Battery Operated*
- *Extended Playing Time*
- *Conveniently Located Controls*
- *Headphone Socket*
- *Tone Control*
- *Excellent Sound Reproduction*



PHILIPS

Portable radio



Standard product information

Tuner

- Analogue tuning
- Wave ranges
 - FM 87.5 - 108 MHz
 - MW 525 - 1606.5 kHz
 - LW 150 - 255 kHz
- /04 FM/MW
- /04 FM/MW/LW
- /05 FM/MW/LW
- Ferroceptor for MW (and LW)
- Telescopic aerial for FM (and SW)

Amplifier

- Max. output power 300 mW RMS
- Tone control Music /News

Sound system

- Loud speaker 100 mm
- Metal grill

Power supply

- External supply
 - /00c, /04 230V
 - /05 240V AC
- Batteries 2 x 1.5V, type R20/D cell/UM1

Connections

- Headphone socket 3.5mm

General

- Material Polystyrene, metal grill
- Weight (g) 520
- Dimensions (mm) 210 W x 150H x 78 D
- Quantity/ mastercarton 3

Mains or battery operated

Operates from standard mains supply or from batteries for convenient operation.

Extended playing time

Power-saving technology extends battery playing time up to 300 hours.

Conveniently located controls

Headphone socket

Enable headphones to be used for private listening pleasure, without disturbing others.

Tone control

Varies the bass and treble controls for personal preference.

Excellent sound reproduction

Provides excellent sound reproduction for maximum listening pleasure.

Printed in Hong Kong 2003-01-06
Specifications subject to modification
without notice
2003 © Koninklijke Philips Electronics N.V.
All rights reserved

www.philips.com
www.audio.philips.com

