

Portable radio

AE2170

Portable radio

- **AM/FM splash resistant** radio**

Makes this an ideal radio for bathroom, shower or kitchen

- **Built-in clock function**

High-precision clock lets you keep track of time.

- **Easy to use control**

- **Built-in hanging strap**

*** Not to be immersed or come into continuous contact with water.*



AE2180

Let's make things better.



PHILIPS

Portable radio

AE2170

Standard product information

Tuner

- Analogue tuning
- Wave ranges
 - : FM 87.5 - 108 MHz
 - /04, /14 : MW 525 - 1606.5 kHz
 - /00, /01 : FM/MW
 - /04 : FM/LW
 - /14 : FM (ext.)/LW

- Ferroceptor for MW
- Telescopic aerial for FM

Amplifier

- Max. output power : 300 mW RMS

Speaker system

- Loud speaker : 65 mm

Power supply

- Batteries : 3 x 1.5V , type AA/R6/UM3 cell

General

- Material : Polystyrene, rubber
- Weight : 300 g
- Dimensions : 95 mm W x 150 mm H x 80 mm D
- Quantity/mastercarton : 4

1999-01-19
Printed in Hong Kong
Subject to modification without notice
© 1999 Koninklijke Philips Electronics N.V.
All Rights Reserved

<http://www.philips.com>

Let's make things better.



PHILIPS