



Philips
Portable Radio

FM/MW, Digital tuning
20 one-touch presets
Clock
Battery or AC operated

AE2430

Enjoy your favourite radio

with one-touch access to pre-set stations

Enjoy your favourite FM/MW stations with just a touch with the Philips portable radio. Digital tuning and 20 one-touch presets makes this radio easy to use. The large backlit LCD display provides easy viewing even in low light.

Enjoy your favourite stations

- Digital tuning with preset stations for extra convenience
- Stereo headphone jack for better personal music enjoyment

Easy to use

- Built-in clock function
- Large backlit LCD display for easy viewing in low light
- Built-in speaker to enjoy radio out-loud with a good sound
- Low battery indicator keeping you informed of power level
- Mains or battery operated for flexible placement

PHILIPS

Highlights

Built-in clock


A built-in clock keeps time accurately. When the radio is off, the clock display comes on for added convenience.

Large backlit LCD display




Backlit LCD display ensures easy viewing and operation in low light conditions, and provides clear information at a glance.

Built-in speaker



A speaker offers good sound quality for more pleasure.

Digital tuning with presets



Digital tuning with preset stations for extra convenience

Stereo headphone jack

Connect your own headphones with this Philips device for a more personal listening experience whenever you want it. You can enjoy your favourite music in great sound without disturbing others by connecting your headphones to this device.

Low battery indicator



The low battery indicator lights up when the power is low.

Mains or battery operated



Power your Philips radio set with batteries or a direct mains supply, and enjoy great convenience and flexibility. When a power socket is not available or when you don't want unsightly wires trailing, simply operate the set with batteries. When you need a continuous and stable power supply, connect the set directly to a wall socket. Now you can truly enjoy the freedom of listening wherever you like.

Specifications

Tuner/Reception/Transmission

- Station presets: 20
- Tuner bands: FM, MW, FM stereo
- Tuner enhancement: auto digital tuning

Sound

- Volume control: up/down
- Sound system: stereo
- Output power: 1 W RMS

Connectivity

- Audio/Video output: Headphone (3.5 mm)

Convenience

- Display Digits: 5
- Backlight colour: white
- Display type: LCD display

Accessories

- Cables/Connection: AC-DC adapter
- Others: User Manual

Dimensions

- Master carton quantity: 4
- Product weight: 1.33 kg
- Main unit depth: 76 mm
- Main unit height: 148 mm
- Main unit width: 218 mm

Power

- Battery type: C size (LR14)
- Battery voltage: 1.5 V
- DC input voltage: 9 V
- Number of batteries: 4
- Power supply: 220 - 240 V



Issue date 2022-05-15

Version: 2.1.10

12 NC: 8670 000 58903
EAN: 08 71258 15199 33

© 2022 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com