



Philips
Portable Radio

FM/MW, Digital tuning
Clock display
Battery or AC operated



AE2600B

Enjoy your favourite radio

with one-touch access to pre-set stations

Enjoy your favourite FM/MW stations with just a touch on the Philips portable radio. Digital tuning and five one-touch presets make this radio easy to use. The large backlit LCD display provides easy viewing even in low light.

Enjoy your favourite stations

- FM/MW tuner for radio enjoyment
- Stereo headphone jack for better personal music enjoyment
- Built-in speaker to enjoy radio out-loud with a good sound

Easy to use

- Direct preset keys for quick access to stored radio stations
- Built-in clock function
- Large backlit LCD display for easy viewing in low light
- Low battery indicator keeping you informed of power level
- Mains or battery operated for flexible placement

PHILIPS

Highlights

Built-in clock

A built-in clock keeps time accurately. When the radio is off, the clock display comes on for added convenience.

Large backlit LCD display



Backlit LCD display ensures easy viewing and operation in low light conditions, and provides clear information at a glance.

Stereo headphone jack

Connect your own headphones with this Philips device for a more personal listening experience whenever you want it. You can enjoy your favourite music in great sound without disturbing others by connecting your headphones to this device.

Low battery indicator




The low battery indicator lights up when the power is low.

Mains or battery operated



Power your Philips radio set with batteries or a direct mains supply, and enjoy great convenience and flexibility. When a power socket is not available or when you don't want unsightly wires trailing, simply operate the set with batteries. When you need a continuous and stable power supply, connect the set directly to a wall socket. Now you can truly enjoy the freedom of listening wherever you like.

FM/MW tuner




FM/MW (AM) stereo tuner

Direct preset keys

Direct preset keys for quick access to stored radio stations

Built-in speaker



A speaker offers good sound quality for more pleasure.

Specifications

Tuner/Reception/Transmission

- Station presets: 5 FM, 5 MW
- Tuner bands: FM, MW
- Tuner enhancement: auto digital tuning

Design and finishing

- Colour: Black

Sound

- Volume control: rotary (digital)
- Sound system: mono
- Output power: 1.2 W RMS

Connectivity

- Audio/Video output: Headphone (3.5 mm)

Convenience

- Display Digits: 5
- Backlight colour: white
- Display type: LCD display

Accessories

- Others: User Manual

Dimensions

- Master carton quantity: 4
- Product weight: 0.6 kg
- Main unit width: 139 mm
- Main unit depth: 79 mm
- Main unit height: 186 mm

Power

- Power supply: 220 - 240 V
- Battery voltage: 1.5 V
- Battery type: C size (LR14)
- Number of batteries: 4



Issue date 2017-09-09

Version: 1.0.3

12 NC: 8670 001 22544
EAN: 48 95185 60587 6

© 2017 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com