

Philips
Portable Radio

Modern design
DAB+

AE5230



Great sound from DAB+ radio anywhere

Tune in to Philips portable radio with DAB+ reception for clear sound. Its classic desktop design as well as DAB+ and DAB FM preset stations with quick scan DAB+ radio make this the ideal radio companion.

Enjoy digital quality DAB radio

- DAB for clear and crackle-free radio experience
- DAB and FM compatible for a complete radio experience

Easy to use

- Quick scan of DAB stations for extra convenience
- 10 preset tuning stations
- Large backlit LCD display for easy viewing in low light
- Stereo headphone jack for better personal music enjoyment

PHILIPS

Highlights

DAB



DAB (Digital Audio Broadcasting) digital radio is, on top of FM analog transmission, a new way of broadcasting radio via a network of terrestrial transmitters. It provides listeners with more choices and information delivered in clear and crackle-free sound quality. The technology allows the receiver to lock on to the strongest signal it can be found. With DAB digital stations there are no frequencies to remember, and sets are tuned by station name, so there is no returning on the move.

Quick scan of DAB stations



DAB (Digital Audio Broadcasting) digital radio is, on top of FM analog transmission, a new way of broadcasting radio via a network of terrestrial transmitters. It provides listeners with more choices and information delivered in clear and crackle-free sound quality. The technology allows the receiver to lock on to the strongest signal it can be found. With DAB digital stations there are no frequencies to remember, and sets are tuned by station name, so there is no returning on the move.

10 preset tuning stations

10 preset tuning stations



DAB and FM compatible



DAB (Digital Audio Broadcasting) digital radio is, on top of FM analog transmission, a new way of broadcasting radio via a network of terrestrial transmitters. It provides listeners with more choices and information delivered in clear, crackle-free sound quality. The technology allows the receiver to lock on to the strongest signal it can be found. With DAB digital stations there are no frequencies to remember, and sets are tuned by station name, so there is no returning on the move.

Large backlit LCD display



Backlit LCD display ensures easy viewing and operation in low light conditions, and provides clear information at a glance.

Stereo headphone jack

Connect your own headphone this Philips radio for a more personal listening experience whenever you want it. You can enjoy your favorite movie or music in great sound without disturbing others by connecting your headphones to the player.

Specifications

Tuner/Reception/Transmission

- DAB: info display, smart scan, menu
- Tuner bands: FM, DAB (Band III)
- Station presets: 20
- Antenna: FM antenna
- Tuner enhancement: auto digital tuning

Sound

- Volume control: up/down
- Output power: 300 mW RMS

Loudspeakers

- No. of built-in speakers: 1

Connectivity

- Audio/Video output: Headphone (3.5mm)

Convenience

- Display type: LCD display
- Backlight color: white

Power

- Battery voltage: 1.5 V
- Number of batteries: 6
- Battery type: AA size (LR6)
- Power type: AC Input

Accessories

- Cables/Connection: AC-DC adapter
- Others: Quick start guide, User Manual
- Warranty: Warranty Certificate

Dimensions

- Gross weight: 0.884 kg
- Packaging depth: 90 mm
- Packaging height: 133 mm
- Packaging width: 317 mm
- Weight: 0.65 kg
- Main unit depth: 45 mm
- Main unit height: 104 mm
- Main unit width: 200 mm



Issue date 2014-02-12

Version: 1.0.3

12 NC: 8670 000 59932
EAN: 87 12581 52530 9

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com