

Portable radio

Durable, Jewel like
Metal casing

- Slim, compact design
- FM Stereo and MW (AM) reception
- Stereo in-earphones
- Dynamic bass boost
- Detachable belt clip
- Pouch included



Let's make things better.



PHILIPS

Portable radio



Standard product information

Tuner

- Analogue tuning
- AM/FM stereo
- Frequency ranges
FM 87.5 - 108 MHz
MW 525 - 1607 kHz
(571 - 187 m)
- Ferroceptor for MW
- FM aerial in-earphone
- Wavebands

Amplifier

- Max. output power 2 x 5 m W RMS
- Dynamic Bass Boost (2 position)

Power supply

- Batteries 1 x 1.5V, type
AAA/R03/UM4 cell

Connections

- Headphone socket 3.5mm

Accessories

- In-earphones
- Pouch

General

- Material Polystyrene/Metal
- Weight 55 g
(excluding batteries)
- Dimensions (mm) 45 W x 82 H x 14.5 D
- Quantity/ dealercarton 6
- Quantity/ mastercarton 24

Slim, compact design

High-performance, very compact product that's easy to hold and carry anywhere.

Durable, jewel like metal casing

FM Stereo and MW (AM) reception

Gives you a listening choice of radio stations in high-quality stereo FM and AM reception.

Stereo in-earphones

In-earphone set provides excellent stereo reproduction for maximum music enjoyment.

Dynamic bass boost

Printed in Hong Kong 2000-12-01
Specifications subject to modification without notice
© 2000 Koninklijke Philips Electronics N.V.
All rights reserved

<http://www.philips.com>

Let's make things better.



PHILIPS