



Philips  
Clock Radio

**DAB+**  
FM digital tuner  
Headphone jack



**AE8000**

## Enjoy thousands of Internet radio stations

with DAB+ and FM

Access the world's radio stations with the Philips AE8000. With FM, DAB+ and Internet radio in an elegant and classic wooden design, it is your ideal radio companion.

### **Unlimited listening pleasure - wirelessly**

- Enjoy Internet radio stations to suit your mood
- Clear and crackle-free DAB+ radio
- DAB and FM compatible for a complete radio experience
- Digital tuning with 20 pre-set stations for extra convenience
- Built-in speaker to enjoy radio out-loud with a good sound

### **Easy to use**

- Quick scan of DAB stations for extra convenience
- Big display for easy viewing
- Built-in clock function
- Stereo headphone jack for better personal music enjoyment

**PHILIPS**

Clock Radio  
DAB+ FM digital tuner, Headphone jack

# Highlights

## Free Internet radio stations



The vast collection of free Internet radio stations ensures an endless supply of high-quality music to suit your mood.

## Clear, crackle-free DAB+ radio



DAB+ (Digital Audio Broadcasting) digital radio is, on top of FM analogue transmission, a new way of broadcasting radio via a network of terrestrial transmitters. It provides listeners with more choices and information delivered in clear and crackle-free sound quality. The technology allows the receiver to lock on to the strongest signal it can find. With DAB+ digital stations there are no frequencies to remember, and sets are tuned by station name, so there is no retuning on the move.

## DAB and FM compatible



DAB (Digital Audio Broadcasting) digital radio is a new way of broadcasting radio, in addition


to FM analogue transmission, via a network of terrestrial transmitters. It provides listeners with more choices and information delivered in clear, crackle-free sound quality. The technology allows the receiver to lock on to the strongest signal it can find. With DAB digital stations there are no frequencies to remember, and sets are tuned by station name, so there is no retuning on the move.

## 20-preset digital tuning



Simply tune into the station that you want to preset, then press and hold the preset button to memorise the frequency. With preset radio stations that can be stored, you can quickly access your favourite radio station without having to manually tune the frequencies each time.

## Built-in speaker



A speaker offers good sound quality for more pleasure.

AE8000/10

## Quick scan of DAB stations



DAB (Digital Audio Broadcasting) digital radio is a new way of broadcasting radio, in addition to FM analogue transmission, via a network of terrestrial transmitters. It provides listeners with more choices and information delivered in clear and crackle-free sound quality. The technology allows the receiver to lock on to the strongest signal it can find. With DAB digital stations there are no frequencies to remember, and sets are tuned by station name, so there is no retuning on the move.

## Big display

The large display enables easy readability of the content on the screen. Now you can read the time and alarm easily, even from a distance. It is ideal for the elderly or the visually restricted.

## Built-in clock

A built-in clock keeps time accurately. When the radio is off, the clock display comes on for added convenience.

## Stereo headphone jack

Connect your own headphones with this Philips device for a more personal listening experience whenever you want it. You can enjoy your favourite music in great sound without disturbing others by connecting your headphones to this device.

# Specifications

## Tuner/Reception/Transmission

- DAB: info display, menu, smart scan
- Station presets: 10
- Tuner bands: FM, FM stereo, DAB (Band III), Internet Radio
- Tuner enhancement: auto digital tuning
- Auto digital tuning

## Sound

- Volume control: rotary (digital)
- Sound system: mono
- Output power (RMS): 5 W

## Connectivity

- 3.5 mm headphone jack
- Aux in

## Convenience

- Backlight colour: white
- Display type: LCD display
- Display screen type: Dot Matrix
- Alarms: DAB, FM, Internet Radio

## Accessories

- Cables/Connection: AC-DC adapter
- Others: User Manual
- Quick start guide
- Included accessories: Remote control

## Dimensions

- Master carton quantity: 2
- Main unit height: 116 mm
- Main unit width: 220 mm
- Main unit depth: 143 mm
- Product weight: 1.19 kg
- Packaging dimensions (WxDxH): 287 x 170 x 153 mm
- Weight incl. Packaging: 1.5 kg

## Power

- DC input voltage: 9 V
- Power supply: 220 - 240 V
- Mains power: AC 5.5 V, 1.5 A

## Display

- Resolution: 128 x 64 pixels



Issue date 2017-09-22

Version: 9.0.9

12 NC: 8670 001 23206  
EAN: 48 95185 60637 8

© 2017 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)