

Clock radio

AJ3000

## Battery powered clock radio

- **Weekendsleeper**

*Weekendsleeper can cancel your alarm at weekends....  
sweet dreams!*

- **Battery or adapter operated (not included)**

*Gives you the choice to use 4 AA 1.5V batteries or a 7.5V AC/ DC  
adapter. This enables you to use it as a stationary or as a traveller  
clock radio.*

- **Dual alarm**

*Two alarm times that can be set with the choice of waking up to  
your favourite music from the radio station or from the buzzer.*

- **Extra large LCD display**

- **Backlight control (on/off)**

- **24 hour alarm reset**

- **Quartz controlled clock**

- **9 months battery lifetime**



dual alarm



weekendsleeper



battery powered



The AJ3005 includes adapter



Let's make things better.



PHILIPS

**Standard product information****Clock/alarm**

- Electronic clock : Quartz operated
- /00, /04, /11, /14 : 24 hours
- /01, /15 : 12 hours
- Alarm : Dual alarm (radio & buzzer), repeat alarm, 24-hour alarm reset, weekend sleeper
- Fast and slow, forward and backward time and alarm setting

**Tuner**

- Wavebands : /04 : FM/LW
- /00, /01, /11, /14, /15 : FM/MW
- Frequency ranges : FM 87.5 - 108 MHz
- : MW 525 - 1607 kHz
- : LW 148.5 - 284 kHz

**Amplifier**

- Max. output power (RMS) (±1 dB ; D < 10%) : 100m Watts

**Sound system**

- Loud speaker : 57 mm (2.25")

**Display**

- Multifunctional LCD display with backlight
- Time/day display on LCD
- Backlight control (on/off)
- Slumber indication
- Battery low indication

**Power supply**

- Batteries : 4 x AA, 6 V (not included)
- Self-powered back-up : built-in, 3 minutes
- Adapter included : AJ3005 only (7.5V)

**General AJ3000**

- Material : Polystyrene
- Weight (excl. batteries) : 0.41 Kg
- Weight packed : 0.52 Kg
- Dimensions : 112 mm W x 102 mm H x 83 mm D
- Packaging dimensions : 128 mm W x 114 mm H x 93 mm D
- Quantity /mastercarton : 6

**General AJ3005**

- Material : Polystyrene
- Weight (incl. adapter) : 0.61 Kg
- Weight packed : 0.76 Kg
- Dimensions : 112 mm W x 102 mm H x 83 mm D
- Packaging dimensions : 167 mm W x 128 mm H x 93 mm D
- Quantity /mastercarton : 6

**Product highlights**

- **Extra large LCD display**  
*Bright, backlit display for easy viewing of clock functions.*
- **Backlight control**  
*Enables you to control the backlight of the display for personal preference (on/off).*
- **24 hour alarm reset**  
*Automatically resets the alarm for the same time on the next day, so you don't have to keep manually resetting the alarm.*
- **Quartz controlled clock**  
*Quartz operated clock which ensures the time stays correct whilst mains frequencies may fluctuate.*
- **Battery low indication**  
*When battery power is too low for backlight activation or playing the radio, the battery low icon will appear flashing on the display. It is still possible to use the clock and alarm function for at least six months from this point onwards.*
- **Wake up to radio or buzzer**  
*Gives you the choice of waking up to your favourite radio station or alarm buzzer.*
- **Slumber**  
*Lets you enjoy up to 30 minutes of radio entertainment while going to sleep. After the pre-set time the radio switches off automatically.*
- **Self-powered back-up**  
*The clock has a self-powered back-up of three minutes, so if you change the batteries, the clock will hold the current, the time and the alarm settings.*
- **Repeat alarm**  
*Switches off the alarm for 5 minutes.*
- **Time and day displayed**
- **9 month battery lifetime**  
*(depending on the usage of the radio)*