



Clock radio

Large LED display

- Easy alarm/ time set
- Wake up to radio or buzzer
- 24 hour alarm reset
- Repeat alarm
- FM/MW or FM/LM tuner
- Sleptimer
- Battery back-up



Let's make things better.



PHILIPS



Clock radio

Standard product information

Clock/ alarm

- Electronic clock
- Wake up by radio or buzzer
- Alarm
 - Single alarm, sleeptimer function, repeat alarm (9 minutes)
- Time/ alarm setting
 - Hours/minutes

Tuner

- FM/AM tuning
- Wavebands
 - /04, /04Z FM/LW
 - /00, /00Z, /05, /09 FM/MW
 - /17 FM/AM
- Frequency ranges
 - FM 87.5 - 108 MHz
 - MW 525 - 1607 kHz
 - LW 148.5 - 284 kHz
 - AM 530 - 1710 kHz

Amplifier

- Max output power (RMS) (+1 dB ; D < 10%)
 - 80 m Watts

Sound system

- Loudspeaker
 - 64 mm (2.5")

Display

- Red LED
 - 0.9" (22.5 mm) digit height

Power supply

- AC Mains
 - /17 120V, 60Hz
 - /00, /00Z, /04, /04Z, /05, /09 230V, 50 Hz
- Backup battery
 - 6F22, 9V (not included)

General

- Material
 - Polystyrene
- Weight
 - 0.5 kg
- Dimensions (mm)
 - 185 W x 53 H x 148 D
- Packaging dimensions (mm)
 - 197 W x 63 H x 197 D
- Quantity/mastercarton
 - 6

Large LED display

Easy alarm/ time set

Wake up to radio or buzzer

Gives you the choice of waking up to your favourite radio station or alarm buzzer.

24 hour alarm reset

Automatically resets the alarm for the same time on the next day, so you don't have to keep manually resetting the alarm.

Repeat alarm

Switches off the alarm for 9 minutes.

FM/MW or FM/LM tuner

Sleeptimer

Battery back-up

Printed in Hong Kong 2000-12-01
Specifications subject to modification without notice
© 2000 Koninklijke Philips Electronics N.V. All rights reserved

<http://www.philips.com>

Let's make things better.



PHILIPS