

Fashion clock radio

- **Wake up to radio or buzzer**

Gives you the choice of waking up to your favorite radio station or alarm beeper.

- **Gentle wake; increasing alarm volume**

When you wake up with the beeper, the volume will increase gradually which ensures you will have a gentle and certain wake.

- **Repeat alarm**

Switches off the alarm for 9 minutes.

- **24 hour alarm reset**

Automatically resets the alarm for the same time on the next day, so you don't have to keep manually resetting the alarm.

- **Sleeptimer**

- **Easy alarm/ time set**

- **Battery back-up**



gentle wake



Standard product information**Clock/alarm**

- Electronic clock
- Quartz-operated clock : 11, /14
- Wake up to radio or buzzer
- Alarm : Single alarm (radio and buzzer)
- Gentle wake; increasing alarm volume
- 24-hour alarm reset
- Repeat alarm
- Time/ alarm setting : Hours/ minutes

Tuner

- FM/AM tuning
- Wavebands
 - /00, /01, /05, /09, /10, /11, /13 : FM/MW
 - /04 : FM/LW
 - /14 : ext.FM/MW
 - /17 : FM/AM
- Frequency ranges
 - /14 : FM 87.5 - 108 MHz
 - /14 : Fm 65 - 108 MHz
 - : MW 525 - 1607 kHz
 - : LW 148.5 - 284 kHz
 - : AM 530 - 1710 kHz

Amplifier

- Max. output power (RMS) (+ dB; D < 10%) : 80m Watts

Sound system

- Loudspeaker : 64 mm (2.5")

Display

- Green LED : 0.6" (15mm) digit height
- Clock type
 - /00, /04, /05 : 24 hours
 - /09, /11, /14 : 24 hours
 - /01, /10, /13, /17 : 12 hours with pm indication

Power supply

- AC Mains
 - /01, /11 : 120/230V, 50/60 Hz (switchable)
 - /00, 04, /05, /09, /14 : 230V, 50Hz
 - /10 : 240V, 50 Hz
 - /13 : 220V, 60 Hz
 - /17 : 120V, 60Hz
- Back-up battery : 6F22, 9V (not included)

General

- Material : Polystyrene
- Weight : 560g
- Dimensions : 106 mm W x 158 mm H x 98 mm D
- Packaging dimensions : 160 mm W x 190 mm H x 140 mm D
- Quantity/ mastercarton : 6

Product highlights

- **Wake up to radio or buzzer**
Gives you the choice of waking up to your favorite radio station or alarm beeper.
- **Gentle wake; increasing alarm volume**
When you wake up with the beeper, the volume will increase gradually which ensures you will have a gentle and certain wake.
- **Repeat alarm**
Switches off the alarm for 9 minutes.
- **24 hour alarm reset**
Automatically resets the alarm for the same time on the next day, so you don't have to keep manually resetting the alarm.
- **Sleeptimer**
- **Easy alarm/ time set**
- **Battery back-up**