

Clock radio



Analogue alarm time clock

- Alarm by radio or buzzer
- Front alarm setting
- Built in FM/AM tuner
- Repeat alarm
- Gentle wake
- Clock light



Let's make things better.



PHILIPS



Clock radio

Standard product information

Clock/ alarm

- Analogue clock
- Wake up by radio or buzzer
- Front alarm setting
- Alarm Single alarm, sleeptime function (approx 60 minutes)
- Repeat alarm

Tuner

- FM/AM tuning
- Waveband FM/MW (/00C)
 FM/LW (/04)

Frequency ranges

- FM 87.5 - 108 MHz
- MW 525 - 1607 kHz
- LW 148.5 - 284 kHz

Amplifier

- Max output power (RMS) 80 mW

Sound system

- Loudspeaker 57 mm (2")

Power supply

- Radio 2 x 1.5 V DC battery
 AA/R6/LM-3
 (not included)
- Clock 1 x 1.5 V DC battery
 AA/R6/LM-3
 (not included)

General

- Material Polystyrene
- Weight 390 g
- Dimensions (mm) 110 W x 105 H x 95 D
- Packaging dimensions (mm) 126 W x 126 H x 126 D
- Quantity/mastercarton 6

Alarm by radio or buzzer

Front alarm setting

Easily set the alarm time by rotating the ring on the front of the clock.

Built in FM/AM tuner

Repeat alarm

Gentle wake (increasing alarm volume)

Gentle Wake lets you customise your alarm volume to the level you need to wake up. When the wake-up time arrives, the alarm will switch on and the volume will gradually increase between the levels you've selected, until the sound wakes you up.

Clock light

Printed in Hong Kong 2002-03-15
Specifications subject to modification without notice
© 2002 Royal Philips Electronics
All rights reserved

www.philips.com
www.audio.philips.com

Let's make things better.



PHILIPS