

Clock radio



# Dual alarm

- Large LED display
- Easy alarm/time set
- Wake up to radio or buzzer
- 24 Hour alarm reset
- FM/MW or FM/LW tuner
- Sleptimer
- Battery back-up
- Repeat alarm



*Let's make things better.*



**PHILIPS**



# Clock radio

## Standard product information

### Clock/ alarm

- Electronic clock
- Wake up by radio or buzzer
- Alarm
  - Dual alarm, repeat alarm (9 minutes), sleeptimer, 24 hour alarm reset
- Fast forward/ slow reverse time and alarm set

### Tuner

- FM/AM tuning
- Wavebands
  - /00, /09 FM/MW
  - /17 FM/AM
- Frequency ranges
  - FM87.5 - 108MHz
  - MW525 - 1607 kHz
  - LW148.5 - 284 kHz

### Amplifier

- Max. output power (RMS)  
(+ 1 dB; D<10%) 80m Watts

### Sound system

- Loud speaker 64mm (2.5")

### Display

- Red LED 0.9" (22.5mm) digit height

### Power supply

- AC mains
  - /00, /09 230V, 50Hz
  - /17 120V, 60Hz
- Backup battery 6F22, 9V (not included)

### General

- Material Polystyrene
- Weight 0.5 Kg
- Dimensions (mm) 185 W x 53 H x 148 D
- Packaging dimension (mm) 197 W x 63 H x 197 D
- Quantity/mastercarton 6

### Dual alarm

Two alarms that can be set independently with the choice of waking up to your favourite music from the radio station or from the buzzer.

### Large LED display

### Easy alarm/time set

### Wake up to radio or buzzer

Gives you the choice of waking up to your favourite radio station or alarm buzzer.

### 24 Hour alarm reset

Automatically resets the alarm for the same time on the next day, so you don't have to keep manually resetting the alarm.

### FM/MW or FM/LW tuner

Gives you a wide selection of radio stations to choose from.

### Sleeptimer

### Battery back-up

### Repeat alarm

Switches off the alarm for 9 minutes

Printed in Hong Kong 2000-12-01  
Specifications subject to modification without notice  
© 2000 Koninklijke Philips Electronics N.V.  
All rights reserved

<http://www.philips.com>

Let's make things better.



PHILIPS