

Clock radio

Dual alarm



- Green LED display
- Easy alarm/time set
- Wake up to radio or buzzer
- 24 Hour alarm reset
- FM/MW or FM/LW tuner
- Sleptimer
- Battery back-up
- Repeat alarm



Let's make things better.



PHILIPS



Clock radio

Standard product information

Clock/ alarm

- Electronic clock
- Wake up by radio or buzzer
- Alarm
 - Dual alarm, repeat alarm (9 minutes), sleeptimer, 24 hour alarm reset
- Fast forward/ slow reverse time and alarm set

Tuner

- FM/Am tuning
- Wavebands
 - /00, /04, /05, /09 FM/MW
 - /17 FM/AM
- Frequency ranges
 - FM 87.5 - 108MHz
 - MW 525 - 1607 kHz
 - LW 148.5 - 284 kHz

Amplifier

- Max. output power (RMS) (+ 1 dB; D<10%) 80m Watts

Sound system

- Loud speaker 64mm (2.5")

Display

- Green LED 0.9" (22.5mm) digit height for /17
- Green LED 0.6" (15mm) digit height for /00, /04, /05

Power supply

- AC mains
 - /00, /04, /05, /09 230V, 50Hz
 - /17 120V, 60Hz
- Backup battery 6F22, 9V (not included)

General

- Material Polystyrene
- Weight 0.5 Kg
- Dimensions (mm) 180 W x 43 H x 162 D
- Quantity/mastercarton 6

Dual alarm

Two alarms that can be set independently with the choice of waking up to your favourite music from the radio station or from the buzzer.

Easy alarm/ time set

Wake up to radio or buzzer

Gives you the choice of waking up to your favourite radio station or alarm buzzer.

24 Hour alarm reset

Automatically resets the alarm for the same time on the next day, so you don't have to keep manually resetting the alarm.

FM/MW or FM/LW tuner

Gives you a wide selection of radio stations to choose from.

Sleeptimer

Battery back-up

Repeat alarm

Switches off the alarm for 9 minutes

Printed in Hong Kong 2000-12-01
Specifications subject to modification without notice
© 2000 Koninklijke Philips Electronics N.V.
All rights reserved

<http://www.philips.com>

Let's make things better.



PHILIPS