

Short Service Book Template

Date: 2007-05-31 v1.1

Service-chassis-name: AJ3230



Development-chassis-name: **Clock Radio**

Product-description + key features **Technical specifications**

Sound

- Output power (RMS): 100mW
- Sound System: Mono
- Volume Control: rotary

Tuner/Reception/Transmission

- Antenna: AM Antenna, FM Antenna
- Auto digital tuning: no
- Tuner Bands: FM, MW

Convenience

- Alarms: 24 hour alarm reset, Buzzer Alarm, Gentle Wake, Radio Alarm, Repeat alarm (snooze), Sleep timer
- Backlight color: Amber
- Display Digits: 4
- Display Type: OLED

Accessories

- Included Accessories: User Manual, Warranty certificate

Dimensions

- Packaging dimensions (W x H x D): 0 x 0 x 0 mm
- Packaging type: D-box
- Product dimensions (W x H x D): 125 x 144 x 63 mm
- Product weight: 0.65 kg

Power

- Battery type: AA, LR6
- Battery voltage: 1.5 V
- Mains power: no
- Number of batteries: 2

Successor of: 2002 model

Complete new/derived: 2002 model

Own-designed product or OEM: OEM

Supplier/Development lab (BLC): CMT

Sales per region per CTN:	Model	Stk	Region	FMS Plan	Total Qty	Going Price
	AJ3230	/00	Europe	2002Q2	TBC	TBC
	AJ3230	/04	Europe	2002Q2	TBC	TBC
	AJ3230	/05	Europe	2002Q2	TBC	TBC
	AJ3230	/17	Nafta	2002Q2	TBC	TBC
	AJ3230	/79	APAC	wk707	TBC	TBC

Planning: CS 2002
PRS 2002
CR Nov'2002

Service-offering: OCX / CCB - all region

Estimated CPI at PRS: Not applicable

Field-call rate breakdown: Not applicable as 2002 model, cannot find FCR data now

Accessory List **12NC** **Accessory description**
No service spare part is available

Customer Package @ CR Leaflet, DFU, FAQ, SBOM, Service Manual (Service Manual is not applicable for OCX product)