

Clock Radio

AJ3380

Clock Radio

- **Dual Alarm**

Two alarms that can be set independently with the choice of waking up to your favourite music from the radio station or from the buzzer.

- **Repeat Alarm**

Switches off the alarm for 9 minutes.

- **Alarm Reset**

Automatically resets the alarm for the same time on the next day, so you don't have to keep manually resetting the alarm.

- **Dynamic Bass Boost**

- **Large Green Display with Brightness Control**

- **Easy Alarm/Time Set**

- **Battery Back-up**



Let's make things better.



PHILIPS

Clock Radio

AJ3380

Standard product information

Clock/Alarm

- Electronic clock
- Wake up by radio or buzzer
- Alarm : Dual alarm (radio & buzzer),
Slumber function, Repeat alarm (9 minutes)
- Time/alarm setting : Fast forward/slow reverse

Tuner

- FM/AM tuning
- Wavebands : /04 : FM/LW
/00, /01 : FM/MW
/10 : FM/AM
- Frequency ranges : FM 87.5 - 108 MHz
MW 525 - 1607 kHz
LW 148.5 - 284 kHz
AM 530 - 1710 kHz

Amplifier

- Max. output power (RMS)
(±1 dB ; D < 10%) : 300 m Watts

Sound System

- Loudspeaker : 76 mm (3")

Display

- Green LED : 1.4" (36 mm) digit height
- Clock indication : 24 hours
/01, /10 : 12 hours with pm indication

Power Supply

- AC mains : /01 : 120/230 V, 50/60 Hz (switchable)
/00, /04 : 230 V, 50 Hz
/10 : 240 V, 50 Hz
- Backup battery : 6F22, 9 V (not included)

General

- Material : Polystyrene
- Weight : 0.9 Kg
- Dimensions : 220 mm W x 107 mm H x 118 mm D
- Packaging dimensions : 252 mm W x 134 mm H x 155 mm D
- Quantity /mastercarton : 3

Product Highlights

• Large Green Display with Brightness Control

Large 36 mm display with clock functions that are bigger and brighter for easier viewing.

• Wake Up to Radio or Buzzer

Gives you the choice of waking up to your favourite radio station or alarm buzzer.

• FM/MW or FM/LW Tuner

Gives you a wide selection of radio stations to choose from.

• Slumber

Lets you enjoy up to 59 minutes of radio entertainment while going to sleep.

After the pre-set time the radio switches off automatically.

• Dynamic Bass Boost

Enhances bass tone frequencies to give deep, rich sounds.

• Large Green Display with Brightness Control

• Battery Back-Up

A 9-Volt battery (not included) ensures that clock and alarm settings are maintained in the event of a mains interrupt or failure. Should this happen the display will not illuminate but the alarm and clock settings remain active.

• Easy Alarm/Time Set

• Radio On/Off Switch

98-03-30

Subject to modification without notice
© 1998 Philips Electronics N.V.
All Rights Reserved

<http://www.philips.com>

Let's make things better.



PHILIPS