



Auto time-set AM/FM Clock radio

Auto time-set clock radio

- LCD touch screen control
- Radio controlled clock for auto time adjustment
- Digital tuner with 15 station presets
- Super big LCD for easy reading
- Two colours LCD display for current time and alarm time
- Dual alarm
- Alarm time display
- Gentle wake
- Repeat alarm
- Sleptimer
- Wake up to radio or buzzer
- 24 hour alarm reset



Let's make things better.



PHILIPS



Auto time-set AM/FM Clock radio

Standard product information

Clock/ alarm

- Radio controlled clock
- Clock indication 24 hours (/00)
- Radio clock code format DCF 77

Alarm

- Dual alarm (radio & buzzer)
- Gentle wake (for buzzer only)
- Sleptimer function
- Repeat alarm
- 24-hour alarm reset

Tuner

- Digital tuning
- 15 radio station presets
- Wavebands FM/MW/LW (/00)

Frequency ranges

- FM 87.5 - 108 MHz
- MW 531 - 1602 kHz
- LW 148 - 284 kHz
- Radio clock frequency at Frankfurt 77.5 kHz

Amplifier

- Max. output power (RMS) (+1 dB; D<10%) 100 mW

Sound system

- Loudspeaker 64 mm (2.25")

Display

- LCD touch panel control
- Multifunctional LCD with backlight
- Brightness control

Connection

- Headphone socket 3.5 mm

Power supply

- AC adapter included
- /00 - 230 V, 50 Hz
- Self-powered back up built in, 3 minutes

General

- Material Polystyrene
- Weight 0.48 kg
- Dimensions (mm) 135 W x 40 H x 165 D
- Packaging dimensions (mm) 160 W x 61 H x 280 D
- Quantity/Mastercarton 6

LCD touch screen control

Radio controlled clock for auto time adjustment

The radio controlled clock receives time signals from a long wave radio station in Germany. This allows the clock to calibrate its time with the atomic time scale clock at the transmitter, and to set and display the correct time accordingly.

Digital tuner

By allocating favourite stations a preset number, it's quick and convenient to return to them without having to remember frequencies. Digital tuner preset combinations include 15 FM or MW presets.

Super big LCD for easy reading

2-Colour display for current time and alarm time

To distinguish between the current time and the alarm time setting, the alarm time has an amber background and the actual time's background is green. The time backlight is constantly on, the alarm time backlight only shows when the alarm is activated.

Dual alarm

Two alarms that can be set independently, with the choice of waking up to your favourite music from the radio station or from the buzzer.

Alarm time display

A continuous display shows both the current time and the time that the alarm is set to go off, giving constant reassurance to the alarm user.

Gentle wake (increasing alarm volume)

Gentle Wake lets you customise your alarm volume to the level you need to wake up. When the wake-up time arrives, the alarm will switch on and the volume will gradually increase between the levels you've selected, until the sound wakes you up.

Repeat alarm

Sleep timer

Sleep timer can be programmed to allow music to play for any period up to 60 minutes. Once the selected time period has expired, the machine switches to stand-by mode.

Wake up to radio or buzzer

Gives you the choice of waking up to your favourite radio station or alarm buzzer.

24 hour alarm reset

Automatically resets the alarm for the same time on the next day, so you don't have to keep manually resetting the alarm.

Brightness control

Enables you to control the brightness of the display for personal preference.

Headphone connection

Self-powered back-up

The clock has a self-powered back-up of three minutes, so in case of power failure, the clock will hold the time and the alarm settings.

Printed in Hong Kong 2002-03-15
Specifications subject to modification
without notice
© 2002 Royal Philips Electronics
All rights reserved

www.philips.com
www.audio.philips.com

Let's make things better.



PHILIPS