


CASSETTE CLOCK RADIO



CASSETTE CLOCK RADIO

AJ 3840 /00 FM, MW and LW 24 hour
clock
/10 FM and MW, 12 hour clock
/17 FM and AM, Magnavox,
12 hour clock

- Cassette play back
- Dual alarm
- Wake by buzzer/radio/cassette
- Green LED display/brightness control (high/low)
- Slumber and repeat alarm functions
- 24 Hour alarm reset



PHILIPS

Standard product information**RADIO**

- Sensitive radio reception on FM and AM. FM wire and AM ferroceptor aerials. Thumbwheel tuning and slider waveband switch
- Thumbwheel volume control, loud, good quality sound from a large built-in loudspeaker.
- Separate radio on and off switches.

CLOCK

- Precision electronic clock runs independently of radio. Digital green LED display. Time and alarm settings.
- Power back-up keeps the clock running if the set is disconnected or the mains is interrupted.
- Slider switch for alarm mode setting (cassette, radio and buzzer).
- Repeat alarm will switch off the alarm for 9 minutes. If the repeat alarm is not pressed, the alarm will switch off after 59 minutes.
- Slumber enables you to listen to the radio or cassette for maximum 59 minutes and switches off the radio or cassette automatically after the slumber time.
- Alarm reset enables you to switch off the alarm for 24 hours. That means the alarm will come off automatically the following morning.

CASSETTE

- Cassette playback
- Auto-stop in playback
- Fast forward and rewind function

CLOCK SECTION

Clock	: Electronic
Display	: Green LED with brightness control (high/low)
Hour indication	
/00	: 24 hours
/10 and /17	: 12 hours with AM/PM indication

RADIO SECTION

Wave ranges AJ 3920	
/00	: FM 87.5 - 108 Mhz
	: MW 526.5 - 1606.5 kHz
	: LW 148.5 - 283.5 kHz
/10, /17	: FM 87.5 - 108 Mhz
	: MW 526.5 - 1606.5 kHz
Aerials	: Ferroceptor for MW (and LW)
	: Wire aerial for FM

AMPLIFIER SECTION

Max. output power (RMS) (± 1 dB; D<10%)	: 400 m Watt
--	--------------

CASSETTE SECTION

System	: Compact cassette
Cassette tap	: Normal (type 1) tape
Keys	: Play/stop/F.fwd/rew.

CONNECTIONS

Headphone	: 3,5 mm socket
-----------	-----------------

POWER SUPPLY

AC mains	
/00	: 220 - 230 V, 50 Hz
/10	: 240 V, 50 Hz
/17	: 110 V, 60 Hz
Backup battery (not included)	: 9 V, type 6F22

CABINET

Material	: Polystyrene
Dimensions (w x h x d)	: 245 x 60 x 163 mm
Net. weight/product	: 1,04 kg
Gross Weight/	
master carton	: 7,6 kg
Quantity per:	
master carton	: 6 sets
20 ft container	: 3564 sets
40 ft container	: 7128 sets

Subject to modification without notice

Printed in Holland

3122 321 6761 2


PHILIPS