



Philips
Clock Radio

Big display

DAB+/FM, Digital tuning
Alarm
Time & alarm backup



AJB3552

Wake up to clear and crackle free DAB+ radio

Wake up to multiple-source music with a large LCD display Philips Clock radio. A built-in clear & crackle free DAB+ radio brings you more stations with rich warming music. Three dials in front let you set up the time and alarm effortlessly.

Enjoy digital quality DAB radio

- Digital Radio for clear and crackle-free radio experience
- DAB and FM compatible for a complete radio experience
- Digital tuning with preset stations for extra convenience
- Dynamic Bass Boost for deep and dramatic sound

Easy to use

- Easy clock set for instruction-free time and alarm setup
- Auto-dimming light sensor for comfort viewing experience
- Auto time synchronization ensures accurate time without fuss
- Large backlit LCD display for easy viewing in low light


Everything you need

- Wake up to your favorite radio tune or a buzzer
- Sleep timer automatically turns off radio at a preset time
- Adjustable repeat alarm for flexible extra-snooze time
- Gentle wake for a pleasant wake up experience

PHILIPS

Highlights

DAB and FM compatible



DAB (Digital Audio Broadcasting) digital radio is, on top of FM analog transmission, a new way of broadcasting radio via a network of terrestrial transmitters. It provides listeners with more choices and information delivered in clear, crackle-free sound quality. The technology allows the receiver to lock on to the strongest signal it can be find. With DAB digital stations there are no frequencies to remember, and sets are tuned by station name, so there is no returning on the move.

Auto-dimming light sensor



Always be assured of being able to read the display, whatever time of day it is. The built-in light sensor reads the intensity of ambient light and then determines how bright the display needs to be to ensure clarity. During the day, or under strong lighting, the brightness automatically increases so you can see the display easily against the surrounding flood of light. At night, or under very low light conditions, the display softens, allowing you to look at the display without discomfort, and


letting you sleep without being disturbed by glare.

Dynamic Bass Boost



Dynamic Bass Boost maximizes your music enjoyment by emphasizing the bass content of the music throughout the range of volume settings - from low to high - at the touch of a button! Bottom-end bass frequencies usually get lost when the volume is set at a low level. To counteract this, Dynamic Bass Boost can be switched on to boost bass levels, so you can enjoy consistent sound even when you turn down the volume.

Auto time synchronization



With the automatic time setting function in your clock radio, you do not ever have to set the time. The clock synchronizes with radio signals automatically, even when it is switched off. It updates itself within one minute when there is an immediate need for adjustment, and makes routine synchronizations with radio signals to ensure it keeps accurate time always. From the first time you take the clock radio out of the box, to the time a power outage occurs, you can depend on your Philips

product to give you the right time, fuss-free and reliably.

Gentle wake



Start your day right by waking up gently to a gradually escalating alarm volume. Normal alarm sounds with a preset volume are either too low to wake you up or are so uncomfortably loud that you are rudely jolted awake. Choose to wake up to your favorite music, radio station or buzzer alarm. Gentle wake's alarm volume gradually increases from subtly low to reasonably high in order to gently rouse you.

Easy clock set

The time and alarm are so easy to set up that referring to the Quick Start Guide or Instruction For Use may not be necessary. Simply refer to the Clock radio's silkscreen buttons to set the time and alarm.

Large backlit LCD display



Backlit LCD display ensures easy viewing and operation in low light conditions, and provides clear information at a glance.

Specifications

Tuner/Reception/Transmission

- DAB: Band III, Info display, Smart Scan, Menu
- Tuner Bands: FM
- Auto digital tuning
- Station presets: 20 (FM), 20 (DAB)
- Antenna: FM Antenna

Sound

- Volume Control: Volume Control rotary/encoder
- Output power (RMS): 1.5W
- Sound System: Mono

Convenience

- Display Type: LCD
- Backlight color: White
- Alarms: 24 hour alarm reset, Buzzer Alarm, Gentle Wake, Radio Alarm, Repeat alarm (snooze), Sleep

- timer
- Clock/Version: Digital

Power

- Mains power: AC mains
- Power supply: 100-240VAC, 50/60Hz

Accessories

- Included accessories: User Manual, Quick start guide, AC-DC Adapter, Warranty certificate

Dimensions

- Product dimensions (W x H x D):
172 x 92 x 63 mm
- Packaging dimensions (W x H x D):
245 x 105 x 82 mm
- Packaging type: D-box



Issue date 2014-06-24

Version: 1.0.6

12 NC: 8670 000 66284
EAN: 87 12581 55672 3

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com