

Philips
Radio Cassette Recorder



AQ4150

Portable radio cassette player

Handy radio cassette recorder that's easy to take with you anywhere, thanks to the big, fold-away carrying handle.

Stereo tuner

- AM/ FM tuner for radio enjoyment

Fully featured recorder

- Fast forward and rewind functions
- Built-in flat mic for excellent quality sound recording
- 3-digit tape counter

Easy to use

- Headphone jack for better personal music enjoyment
- Built-in speaker to enjoy radio out-loud in good sound
- Tone control

PHILIPS

Specifications

Sound

- Output power (RMS): 0.5W
- Sound Enhancement: Tone Control
- Sound System: Mono
- Speaker diameter: 3"
- Volume Control: rotary

Loudspeakers

- Finishing: Metal

Audio Playback

- Cassette Deck Technology: Mechanical
- Cassette Playback Modes: Fast Wind/Rewind, Full

Auto Stop, Pause key, Tape Counter

Audio Recording

- Recording modes: Built-in condenser microphone

Tuner/Reception/Transmission

- Antenna: AM Antenna, FM Antenna
- Tuner Bands: FM, LW, MW

Power

- Battery type: LR14
- Battery voltage: 1.5 V
- Mains power

Highlights

AM/ FM tuner

AM/ FM tuner for radio enjoyment

Fast forward and rewind

Fast forward and rewind functions

Built-in flat microphone

High-quality built-in condenser microphone for excellent quality sound recording

3-digit tape counter

3-digit tape counter

Headphone jack

Headphone jack for better personal music enjoyment

Built-in speaker

A speaker offers good sound quality for more pleasure.

Tone control

Tone control



Issue date 2014-02-05

Version: 1.0.2

12 NC: 9071 541 50009
EAN: 87 10101 19490 5

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com