

Radio cassette recorder

AQ4150

Radio Cassette Recorder

- **AM/FM tuner**

Gives you a wide variety of programmes and music to choose from.

- **Full auto stop**

Automatically shuts off the cassette deck at the end of playback to avoid overstretching the tape and to extend battery life.

- **Tone control**

Varies the bass and treble controls for personal preference.

- **Automatic recording level control**

- **One touch recording**

- **Built-in condenser microphone**

- **Headphone connection**

- **AC/DC operation**



Let's make things better.



PHILIPS

Standard product information**Cassette deck**

- Single cassette deck
- Automatic recording level control
- One touch recording
- Electronic speed control
- Condenser microphone
- Automatic stop
- Normal (type 1) cassette tape

Tuner

- Wave ranges /00S, /01S : FM 87.5 - 108 MHz
MW 526.5 - 1606.5 kHz
- /04S, /05S : FM 87.5 - 108 MHz
AM 526.5 - 1606.5 kHz
LW 148.5 - 283.5 kHz
- /11S : FM 87.5 - 108 MHz
AM 526.5 - 1606.5 kHz
SW1 2.27 - 7.4 MHz
SW2 9.25 - 22.2 MHz
- /14S : FM 64.7 - 108 MHz
AM 526.5 - 1606.5 kHz
LW 148.5 - 283.5 kHz
- Ferroceptor for MW (and LW)
- Telescopic aerial for FM (and SW)
- Automatic frequency control on FM

Amplifier

- Output power : 8 W PMPO, 1W RMS
- Dynamic Bass Boost

Sound system

- Single wide frequency 100 mm (4") loudspeaker

Connections

- Headphone socket : 3.5 mm

Power supply

- Batteries : 4 x 1.5V (D cell)
- AC mains
 - /00S, /04S, /05S, /14S : 220 - 230 V, 50 Hz
 - /01S, /11S : 110 - 127/220 - 240 V
(switchable), 50 - 60 Hz
 - /10S : 230 - 240 V, 50 Hz

General

- Weight : 1.3 Kg
- Weight packed : 1.7 Kg
- Dimensions : 335 mm W x 170 mm H x 160 mm D
- Packagaging dimensions : 400 mm W x 175 mm H x 165 mm D
- Quantity /mastercarton : 4

Product highlights

- **Tone control**
Varies the bass and treble controls for personal preference.
- **Automatic recording level control**
Electronic circuit that constantly monitors the input signal to ensure accurate, distortion-free recording.
- **One touch recording**
- **AC/DC operation**
Operates either on batteries or mains supply, using the detachable AC power cord.
- **Headphone connection**
Enables stereo headphones to be used for private listening pleasure. Automatically switches off speakers when used.