



Philips
Portable Radio/Cassette
Rec.

AQ6345

Record your ideas wherever you are

Capture your thoughts on tape with this handy, pocket-size memo recorder.

Fully featured recorder

- Voice-activated recording
- Built-in flat mic for excellent quality sound recording
- LED lights up to indicate that recording is in progress

Loud, good quality sound

- Background noise suppression
- Built-in speaker to enjoy radio out-loud in good sound

Easy to use

- Fast forward and rewind functions
- 3-digit tape counter
- Headphone jack for better personal music enjoyment

PHILIPS

Specifications

Sound

- Output power (RMS): 150mW
- Sound Enhancement: Noise Reduction
- Sound System: Stereo
- Volume Control: rotary

Audio Playback

- Cassette Deck Technology: Mechanical
- Cassette Playback Modes: Cue, Fast Wind/Rewind, Full Auto Stop, Pause key, Tape Counter
- Number of decks: 1

Audio Recording

- Recording Media: Tape



Connectivity

- DC in: 3V
- Headphone: 3.5 mm

Dimensions

- Product dimensions (W x H x D): 91 x 112 x 34 mm
- Product weight: 0.24 kg

Power

- Battery type: AA, R6
- Battery voltage: 1.5 V
- Number of batteries: 2

Highlights

Voice-activated recording

Voice-activated recording

Built-in flat microphone

High-quality built-in condenser microphone for excellent quality sound recording

Recording with LED indicator

LED lights up to indicate that recording is in progress

Background noise suppression

Background noise suppression

Built-in speaker

A speaker offers good sound quality for more pleasure.

Fast forward and rewind

Fast forward and rewind functions

3-digit tape counter

3-digit tape counter

Headphone jack

Headphone jack for better personal music enjoyment



Issue date 2014-02-05

Version: 1.0.2

12 NC: 9071 663 45009
EAN: 87 10101 36661 6

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com