



Cassette Recorder

- **Cue, Review, Fast Forward and Rewind Functions**

Search the tape using either the forward and rewind functions, or for a faster audible search, the cue and review controls.

- **One-Touch Recording**

Offers the convenience of making recordings with the touch of a single control.

- **Tone Control for Bass and Treble**

Manual adjustment of the tone control modifies bass and treble frequencies of the audio output signal, providing fast, easy custom settings for the user's listening pleasure.

- **Tape Counter**

- **Battery-Level Indication**

- **Full Auto Stop**

- **Built-In Microphone**

- **Automatic Recording Level Control**

- **Variable Pitch Control**



Let's make things better.



PHILIPS

Standard product information**Cassette Deck**

- Motor : DC, electronic control
- Tape speed : standard 4.76 cm/sec.
- Pitch control for adjusting tape speed
- 6-key cassette recorder
- Cue and review functions
- 3-digit tape speed counter
- Automatic recording level control
- Tone control for bass and treble
- Battery-level indication
- Full automatic stop
- Normal (type 1) cassette tape
- Signal-to-noise ratio : 42 dB
- Track separation : 55 dB

Amplifier

- Max. output power : 2 W RMS
- Treble control : ± 6 dB at 8 kHz
- Bass control : ± 6 dB at 100 kHz

Sound System

- Loud speaker : 100 mm

Power Supply

- Batteries : 6 x 1.5 V batteries, type C, LR14 or UM 2
- AC mains /00, /05 : 220 - 240 V, 50 Hz

Connections

- Headphone socket : 3.5 mm
- Microphone socket : 3.5 mm
- Line in : 3.5 mm
- Loudspeaker socket : 3.5 mm
- External AC mains socket

General

- Material : Polystyrene
- Weight : 1.6 Kg (excluding batteries)
- Dimensions (mm) : 175 mm W x 64 mm H x 265 mm D
- Display box dimensions : 253 mm W x 99 mm H x 302 mm D
- Quantity /mastercarton : 3

Product Highlights

- **Cue, Review, Fast Forward and Rewind Functions**

Search the tape using either the forward and rewind functions, or for a faster audible search, the cue and review controls.

- **One-Touch Recording**

Offers the convenience of making recordings with the touch of a single control.

- **Tone Control for Bass and Treble**

Manual adjustment of the tone control modifies bass and treble frequencies of the audio output signal, providing fast, easy custom settings for the user's listening pleasure.

- **Full Auto Stop**

A mechanism that senses a change in pressure when the tape reaches the end and automatically stops the tape as well as disengaging the transport mechanism.

- **Automatic Recording Level Control**

Automatically determines the optimal recording level to maximize your listening pleasure.

- **Variable Pitch Control**

This feature allows the pitch of sounds to be altered, by changing the speed of the tape.

- **Tape Counter**

- **Battery-Level Indication**

- **Built-In Microphone**

- **Cassette Deck**

- **Headphone Socket**

EAN:

/00- 8710101328966

/05- 8710101328973

Printed in Hong Kong

Subject to modification without notice

<http://www.philips.com>

Let's make things better.



PHILIPS