

Headphone stereo

AQ 6591

## Stereo radio cassette player

- *Smallest in the opening price point of the segment*
- *AM/FM stereo tuner*
- *Dynamic bass boost*
- *Extended playing time (tape playback)*
- *Full auto stop*
- *Stereo in-earphones*
- *High-quality finish*
- *AM/FM stereo tuner*
- *Detachable belt clip*
- *Slim, compact design*



*Let's make things better*



**PHILIPS**

## Standard product information

### Cassette deck

- 3-key stereo cassette deck
- Full automatic stop

### Tuner

- Analog tuning
- Wavebands : AM/FM/FM stereo
- Frequency ranges : FM 87.5 - 108 MHz
- : AM 526.5 - 1606.5 kHz
- : AM 530 - 1710 kHz for /17
- 3mm LED FM stereo indicator
- Wire aerial fr FM via headphone cord
- Ferroceptor for AM

### Amplifier

- Max. output power : 2 x 5 mW RMS
- Dynamic bass boost (2 position)

### Power supply

- Batteries : 2 x 1.5V, type AA/R6/UM3 cell
- Battery life (approx.)
- Tape playback : 18 hours with Philips POWERLIFE batteries
- External supply: 3V DC

### Connections

- Headphone socket : 3.5 mm
- DC in : 3.4 mm, 3V, centre '-'

### Accessories

- Stereo in-earphones
- Stereo headphone for /17
- Detachable belt clip

### General

- Material : Polystyrene
- Weight : 180 g (excluding batteries)
- Dimensions (mm) : 90 mm W x 111mm H x 33 mm D
- Quantity/ mastercarton : 12

## Product highlights

- **AM/FM stereo tuning**  
*Precision tuning system ensures precise, accurate station selection every time.*
- **Dynamic bass boost**  
*Boosts bass response as much as 8 decibels (nearly 3 times more than normal). DBB yields full, rich tonal quality at all volume levels.*
- **Stereo cassette player**  
*Full function stereo cassette with simple, easy-to-use controls.*
- **Lightweight stereo headphones**  
*Enjoy the ultimate stereo listening experience with comfortable stereo headphones that can be conveniently connected to the stereo headphone jack.*
- **Detachable belt clip**  
*Hands free music wherever you go.*
- **Full auto stop**  
*Automatically shuts off the cassette deck at the end of playback to avoid overstretching the tape and to extend battery life.*
- **Slim, compact design**  
*High-performance, very compact product that's easy to hold and carry anywhere.*
- **High-quality finish**  
*Strong, durable casing, easy-to-operate controls and a very - eye-catching design reflect the high quality of this product.*

1999-12-10  
Printed in Hong Kong  
Subject to modification without notice  
© 1999 Royal Philips Electronics  
All Rights Reserved.

<http://www.philips.com>