

Stereo Radio Cassette Player



Digital stereo radio

- *Dynamic bass boost*
- *AM/FM stereo digital radio*
- *Built-in quartz clock*
- *10-Station preset*
- *Automatic stop*
- *Stereo in-earphones*
- *DC supply connection*
- *Detachable belt-clip*



Let's make things better.



PHILIPS

Stereo Radio Cassette Player



Standard product information

Cassette deck

- 3-key stereo cassette deck
- Full automatic stop

Tuner

- Digital tuner with 10 station presets
- Wavebands AM/FM/FM stereo
- Frequency ranges FM 87.5 - 108 MHz
AM 526.5 - 1606.5 kHz
AM 530 - 1717 kHz for /17
- Wire aerial for FM via headphone cord
- Ferroceptor for AM

Amplifier

- Max. output power 2 x 5 mW RMS
- Dynamic bass boost (2 position)

Display

- Digital LCD display
- Indicator for band, frequency, presets station and stereo

Power supply

- Batteries 2 x 1.5V, type AA/R6/UM3 cell
- External supply 3V DC (not for all versions)

Connections

- Headphone socket 3.5 mm
- DC in 3.4 mm, 3V, centre '-'

Accessories

- Stereo in-earphones
- Stereo headphone for /17
- Detachable belt clip

General

- Material Polystyrene
- Weight 190g (excluding batteries)
- Dimensions 113 mm W x 90 mm H x 33 mm D
- Quantity/dealercarton 6
- Quantity/mastercarton 12

Digital stereo radio

Dynamic bass boost

Enhances bass tone frequencies to give deep, rich sounds.

AM/FM stereo digital radio

Built-in quartz clock

High-precision clock with digital display lets you keep track of time.

10-Station preset

Provides fast, accurate tuning of up to 5 FM and 5 AM stations of your choice.

Automatic stop

Automatically shuts off the cassette deck at the end of playback to avoid overstretching the tape and to extend battery life.

Stereo in-earphones

Printed in Hong Kong 2001-02-01
Specifications subject to modification
without notice
© 2001 Koninklijke Philips Electronics N.V.
All rights reserved

<http://www.philips.com>

Let's make things better.



PHILIPS