

Stereo Radio Cassette Player

AQ6681

Stereo Radio Cassette Player

- **Digital Synthesized AM/FM Stereo Tuner**

Locks on to the most powerful signal for high-quality, drift-free reception.

- **Dynamic Bass Boost**

Enhances bass tone frequencies to give deep, rich sounds.

- **10-Station Preset Tuning**

Provides fast, accurate tuning of up to 5 FM and 5 AM stations of your choice.

- **Extended Playing Time (Tape Playback)**

Extended Playing Time (tape playback)

Innovative, power-saving technology extends battery playing time to 18 hours (2 "AA" batteries)*.

- **Digital LCD Display**

- **Full Auto Stop**

- **Detachable Belt Clip**

- **Stereo In-earphones**

- **High-Quality Finish**

- **Slim, Compact Design**



Let's make things better.



PHILIPS

Stereo Radio Cassette Player

AQ6681

Standard product information

Cassette Deck

- 3-key stereo cassette deck
- Full automatic stop

Tuner

- Digital tuner with 10 station presets
- Wavebands : AM/FM/FM stereo
- Frequency ranges : FM 87.5 - 108 MHz
- : AM 526.5 - 1606.5 kHz
- LED tuning indicator
- Wire aerial for FM via headphone cord
- Ferroceptor for AM

Amplifier

- Max. output power : 2 x 5 mW RMS
- Dynamic Bass Boost (2 position)

Display

- Digital LCD display
- Indicator for band, frequency, presets station and stereo

Power Supply

- Batteries : 2 x 1.5 V , type AA/R6/UM3 cell
- External supply : 3 V DC (not for all versions)

Connections

- Headphone socket : 3.5 mm
- DC in : 3.4 mm, 3 V, centre "-"

Accessories

- Stereo in-earphones
- Detachable belt clip

General

- Material : Polystyrene
- Weight : 195 g (excluding batteries)
- Dimensions (mm) : 113 mm W x 90 mm H x 33 mm D

Product Highlights

• Digital LCD Display

Easy-to-read display showing station frequency, etc.

• Full Auto Stop

Automatically shuts off the cassette deck at the end of playback to avoid overstretching the tape and to extend battery life.

• Detachable Belt Clip

For convenient, hands-free music on the move.

• Stereo In-earphones

High-quality in-earphones supplied with unit that offers a wider dynamic range for excellent sound quality.

• High-Quality Finish

Strong, durable casing, easy-to-operate controls and a very eye-catching design reflect the high quality of this product.

• Slim, Compact Design

High-performance, very compact product that's easy to hold and carry anywhere.

**With Philips POWERLIFE batteries*

98-03-27

Subject to modification without notice
© 1998 Philips Electronics N.V.
All Rights Reserved

<http://www.philips.com>

Let's make things better.



PHILIPS