

CD Midi System

AS680C

### 3 CD Changer Midi System with Incredible Surround™

- 800 watts PMPO
- 2 x 50 watts music power
- 2 x 25 watts RMS stereo
- Incredible Surround™
- Dual full logic tape deck
- Auto Replay
- Digital sound control (Optimal, Classic, Rock, Techno, Jazz)
- Dynamic bass boost
- 40 track CD programmability
- FM/MW stereo digital tuner with 40 presets
- 3 way bass reflex speaker system with detachable grilles
- Bedroom clock with wake up alarm

800  
watts PMPO



Incredible  
Surround



KARAOKE



Let's make things better.



PHILIPS

## 3 CD changer midi system

### standard product information

#### amplifier

- 800 watts PMPO
- 2 x 50 watts music power
- 2 x 25 watts RMS,  $\pm 10\%$  THD, 3 ohm, 1kHz
- Incredible Surround™
- digital sound control (optimal, classic, rock, techno, jazz)
- dynamic bass boost

#### compact disc player

- motorized front loading 3 CD changer
- digital servo technology
- bit-check D/A converter
- 40 track CD random program
- play mode (repeat/shuffle/program)
- change 2 discs while playing 1

#### tuner

- FM/MW stereo digital tuner with 40 presets
- auto store for tuner

#### tape deck

- dual full logic tape deck
- auto reverse
- high speed dubbing
- CD synchro recording
- continuous play
- automatic recording level control
- automatic tape type selection
- electronic speed control and full auto stop

#### loudspeaker boxes


- 3-way bass reflex
- 6.25" woofer
- 2.5" tweeter
- detachable grilles

#### connections

- stereo headphones : 3.5mm stereo jack
- video/aux : cinch type sockets

#### general

- fluorescent tube display
- clock/timer
- wake up with CD, tuner or tape
- 23-key remote control



|                      | /21m | /21 | /22 | /30 | /34 |
|----------------------|------|-----|-----|-----|-----|
| Asia Pacific         |      |     |     |     |     |
| Australia/NZ         |      |     |     |     |     |
| Middle East/S Africa |      |     |     |     |     |
| Latam                |      |     | •   |     |     |
| Europe               |      |     |     |     |     |
| E Europe             |      |     |     |     |     |
| <b>tuner</b>         |      |     |     |     |     |
| FM65.81-74MHz        |      |     |     |     |     |
| FM87.5-108MHz        |      |     | •   |     |     |
| MW522-1602kHz        |      |     | •   |     |     |
| FM75 ohm clickfit    |      |     | •   |     |     |
| <b>mains supply</b>  |      |     |     |     |     |
| 120/230V 50-60Hz     |      |     | •   |     |     |
| 230V/50Hz            |      |     |     |     |     |
| <b>general</b>       |      |     |     |     |     |
| made in sticker      |      |     | •   |     |     |

#### Incredible Surround™

Incredible Surround™ magnifies the virtual distance between the speakers. Press the Incredible Surround™ button and the room will be full of good stereo music. No need to move the speakers away from the center unit. For those who don't want to rearrange their lives to fit their hifi.



Product Dimensions:  
363mm W x 422mm H x 375mm D (electronics)  
285mm W x 421mm H x 300mm D (speakers)

Package Dimensions:  
794mm W x 478mm H x 654mm D

Speaker weight : 5.5 kg each

Sett weight : 10 kg

Carton contains: CD Midi System, Multi-Function Remote Control, Batteries, Operating instructions, Warranty information, FM antenna, AM antenna

Printed in Singapore

Date printed : May 1998

Specifications subject to change without notice.

Incredible Surround™ is a Trademark of Philips Consumer Electronics Company