

# PHILIPS

wet and dry electric  
shaver

AquaTouch

DualPrecision blades

Flexing heads

AT753



## Great skin protection, smooth shave

Now enjoy a refreshing shave without worrying about damaging your skin. The Aquatec seal ensures a comfortable dry shave and a refreshing wet shave. Use it wet with shaving gel or foam for enhanced skin comfort.

### **Also use wet for enhanced skin comfort**

- Optimised for use with gel or foam for enhanced skin comfort

### **Protect your skin**

- Glides smoothly over the curves of your face

### **Shave smooth**

- For a comfortably close shave
- Shaves even the shortest stubble

### **Ease of use**

- Washable shaver with QuickRinse system
- 40+ minutes of cordless shaving on one charge

# Highlights

## Aquatec wet & dry



Aquatec seal for a comfortable dry shave and a refreshing wet shave. Optimised for use with shaving gel or foam for enhanced skin comfort, even in the shower.

## Skin Protection System



Rounded low-friction protection heads adjust to the curves of your face to limit skin damage.

## Super Lift & Cut Action



For a close shave, the dual-blade system built into the Philips electric shaver lifts hairs to cut comfortably closer.

## DualPrecision Cutting



DualPrecision shaving heads have slots to shave the normal hairs and holes to shave even the shortest stubble.

## Fully waterproof



With QuickRinse system to clean under the tap and can be used in the shower

## Cordless use 40+ minutes



40+ minutes of cordless power for 14 shaves. Fully charges in 8 hours so it's always ready when you are.

# Specifications

## Shaving Performance

Shaving System: Super Lift&Cut

Contour-following: Dynamic contour response

## Ease of use

Display: 1 LED indication, Battery full indication, Battery low indication, Charging indication

Charging: Rechargeable, Cordless operation

Cleaning: Quick rinse hair chamber, Fully waterproof

Shaving time: 40+ minutes

Charging time: 8 hours

## Accessories

Maintenance: Cleaning brush, Protection cap

## Design

Finishing: Decopanel ribbed Black, Front Shell (plain) Black

Colour: Black

Handle: Easy grip, Rubber grip

## Power

Automatic voltage: 100-240 V

Battery type: Li-Ion

Max power consumption: 5.4 W

Stand-by power: 0.5 W

## Service

Replacement head: Replace every 2 yrs with SH50 (these have replaced HQ8)

