

# PHILIPS

electric shaver

AquaTouch

AT754



## Great skin protection, smooth shave wet shave with shaving gel or foam

Enjoy a refreshing shave without worrying about damaging your skin with this wet & dry shaver. The Aquatec seal ensures a comfortable dry shave and a refreshing wet shave. Use it wet with shaving gel or foam for enhanced skin comfort.

### Protect your skin

- Glides smoothly over the curves of your face

### Shave smooth

- For a comfortably close shave

### Ease of use

- 40+ minutes of cordless shaving on one charge
- Washable shaver with QuickRinse system

### Also use wet for enhanced skin comfort

- Optimised for use with gel or foam for enhanced skin comfort

# Highlights

## Aquatec wet and dry



Aquatec seal for a comfortable dry shave and a refreshing wet shave. Optimised for use with shaving gel or foam for enhanced skin comfort, even in the shower.

## Skin Protection System



Rounded low-friction protection heads adjust to the curves of your face to limit skin damage.

## Super Lift & Cut Action



For a close shave, the dual-blade system built into the Philips electric shaver lifts hairs to cut comfortably closer.

## Fully waterproof



With QuickRinse system to clean under the tap and can be used in the shower

## Cordless use 40+ minutes



40+ minutes of cordless power for 14 shaves. Fully charges in 8 hours so it's always ready when you are.

# Specifications

## Shaving Performance

Shaving system: Super Lift and Cut  
Contour-following: Dynamic contour response

## Ease of use

Display: 1 LED indication, Battery full indication, Battery low indication, Charging indication  
Charging: Rechargeable, Cordless operation  
Cleaning: Quick rinse hair chamber, Fully waterproof  
Shaving time: 40+ minutes  
Charging time: 8 hours

## Design

Finishing: Decopanel ribbed Black, Front Shell (plain) Black  
Colour: Black  
Handle: Easy grip, Rubber grip

## Accessories

Maintenance: Cleaning brush, Protective cap

## Service

Replacement head: Replace every 2 yrs with SH50 (these have replaced HQ8)

## Power

Automatic voltage: 100-240 V  
Battery type: Lithium-ion  
Max power consumption: 5.4 W  
Stand-by power: 0.5 W

