

Long battery life CD player



20-hour playback

- Digital dynamic bass boost
- CD-Rewritable compatible
- All CD program modes
- Stereo In-ear headphone and AC/DC adapter included



Let's make things better.



PHILIPS



Long battery life CD player

Standard product information

Amplifier/ system

- Output power (in-ear headphone)
2 x 5mW RMS
- 1-Bit D/A converter for pure sound reproduction
- Dynamic bass boost
- Rotary volume control
- S/N ratio (A weighted) >100 dB
- Frequency response 20 Hz - 20 kHz
- Acoustic feedback

CD player

- 15-Track programmable, shuffle, repeat 1/all
- Search forward/backward with sound
- Resume and hold

LCD display

- Indications for track, time, DBB and CD functions

Connections

- Headphone/line out Stereo, 3.5 mm
- DC in 4.0 mm, 4.5V, centre '+'

Power supply

- Batteries 2 x 1.5V, type AA/LR6/UM3 cell
- Battery playing time 20 hours (regular AA size, alkaline batteries)
- Automatic power switch-off

General

- Material High temperature resistant plastic
- Weight 230 g (excluding batteries)
- Product dimensions (mm) 148 L x 128 W x 26 H
- D-box dimensions /00 (mm) 245 L x 140 W x 49 H
- D-box dimensions /01 /18 /19 (mm) 245 L x 140 W x 54 H
- D-box in clamshell /00z (mm) 295 L x 199 W x 50 H
- Master carton dimensions /00 (mm) 304 L x 253 W x 156 H
- Master carton dimensions /01 /18 /19 (mm) 334 L x 253 W x 156 H
- Master carton dimensions /00z (mm) 341 L x 317 W x 237 H
- Master carton quantity 6

Accessories

- AC/DC adapter
- Stereo in-ear headphone

20-Hour playback (with 2 x AA Alkaline batteries)

Power-saving technology extends battery playing time to 20 hours with two regular LR6-size (AA) alkaline batteries.

Digital dynamic bass boost

Enhances bass at low, mid and high volume, to give deep, rich sounds.

CD-Rewritable compatible

Ensures that both CD-Recordable and CD-Rewritable discs, made by any CD-Recorder, can be played.

All CD program modes

Let you enjoy various CD program modes (repeat one/ repeat all/ shuffle/ repeat shuffle).

Heat resistant body

Unique composite material enables the CD player to withstand very high temperature.

1-Bit D/A converter

Advanced digital conversion technology ensures crystal-clear sound.

Hold

Locks all buttons to prevent interruption of play or change of program settings.

Resume

Bookmark function that ensures the CD starts precisely from the point it was stopped.

Automatic power off

Automatically switches off the CD player at the end of a compact disc.

CD next/ previous

Plays the next or previous track at the touch of a button.

CD music search

Searches the CD at high speed while still producing low-volume sound so you know exactly when to stop.

Repeat one/ all

Repeat the current track or the total CD.

Shuffle

Plays disc selection randomly, giving you each time a new sequence of tracks.

15-track programmable

Stores up to 15 of your favourite tracks for playing back in your order of preference.

Acoustic feedback

Confirms any key-push with friendly beep to acknowledge that a command has been given.

Printed in Hong Kong 2000-12-01
Specifications subject to modification
without notice
© 2000 Koninklijke Philips Electronics N.V.
All rights reserved

<http://www.philips.com>

Let's make things better.



PHILIPS