

Shockproof CD player with 12 sec ESP<sup>4</sup>



# Shockproof

- 22-Hour playback (ESP on, 2 x AA Alkaline batteries)
- Digital dynamic bass boost (2-step)
- CD-Rewritable compatible
- All CD program modes
- Stereo In-ear headphone, belt-clip and AC/DC adapter included



Let's make things better.



PHILIPS

# Shockproof CD player with 12 sec ESP<sup>4</sup>



## Standard product information

### Amplifier/ system

- Output power (in-ear headphone)  
2 x 2.3mW RMS
- 1-Bit D/A converter for pure sound reproduction
- Dynamic bass boost
- Rotary volume control
- S/N ratio (A weighted): >100 dB
- Frequency response: 20 Hz - 20 kHz
- Acoustic feedback

### CD player

- 30-Track programmable, shuffle, repeat 1/all and introscan
- Search forward/ backward with sound
- Resume and hold

### ESP<sup>4</sup> - Fourth generation electronic skip protection

- Electronic skip protection with 12 second memory

### LCD display

- Indications for track, time, 2-stage DBB, CD functions and battery status

### Connections

- Headphone/line out Stereo, 3.5 mm
- DC in 4.0 mm, 4.5V, centre '+'

### Power supply

- Batteries 2 x 1.5V, type AA/LR6/UM3 cell
- Battery playing time 22 hours (ESP on, Alkaline batteries)
- Automatic power switch-off

### General

- Material High temperature resistant plastic
- Weight 211 g (excluding batteries)
- Product dimensions 135 mm L x 125 mm W x 30 mm H
- D-box dimensions /00 (mm) 245 L x 140 W x 49 H
- D-box dimensions /01 /05 /13 (mm) 245 L x 140 W x 54 H
- Master carton dimensions /00 (mm) 304 L x 253 W x 156 H
- Master carton dimensions /01 /05 /13 (mm) 334 L x 253 W x 156 H
- Master carton quantity 6

### Accessories

- AC/DC adapter
- Stereo in-ear headphone
- Belt-clip

### Shockproof

Fourth generation electronic skip protection for continuous music play with 12 second music buffer and upto five times faster shock recovery than conventional systems.

### 22-Hour playback (ESP on, 2 x AA Alkaline batteries)

Powersaving technology extends battery playing time to 22 hours with two regular LR6-size (AA) alkaline batteries.

### Digital dynamic bass boost (2-step)

Enhances bass at low, mid and high volume, to give deep, rich sounds.

### CD-Rewritable compatible

Ensures that both CD-Recordable and CD-Rewritable discs, made by any CD-Recorder, can be played.

### All CD program modes

Let you enjoy various CD program modes (repeat one/ repeat all/ shuffle/ repeat shuffle/ introscan).

### Heat resistant body

Unique composite material enables the CD player to withstand very high temperature.

### 1-Bit D/A converter

Advanced digital conversion technology ensures crystal-clear sound.

### Hold

Locks all buttons to prevent interruption of play or change of program settings.

### Resume

Bookmark function that ensures the CD starts precisely from the point it was stopped.

### Automatic power off

Automatically switches off the CD player at the end of a compact disc.

### CD next/ previous

Plays the next or previous track at the touch of a button.

### CD music search

Searches the CD at high speed while still producing low-volume sound so you know exactly when to stop.

### Repeat one/ all

Repeat the current track or the total CD.

### Shuffle

Plays disc selection randomly, giving you each time a new sequence of tracks.

### 30-track programmable

Stores up to 30 of your favourite tracks for playing back in your order of preference.

### Acoustic feedback

Confirms any key-push with friendly beep to acknowledges that a command has been given.

Printed in Hong Kong 2000-12-01  
Specifications subject to modification  
without notice  
© 2000 Koninklijke Philips Electronics N.V.  
All rights reserved

<http://www.philips.com>

Let's make things better.



PHILIPS