

Jogproof CD player with 45 sec ESP⁴

Jogproof

- 22-Hour playback (ESP on, 2 x AA Alkaline batteries)
- Built-in recharge capability
- Digital dynamic bass boost (2-step)
- CD-Rewritable compatible
- All CD program modes
- Stereo In-ear headphone, belt-clip, ECO-PLUS Ni-MH rechargeable batteries and AC/DC adapter included



Let's make things better.



PHILIPS

Jogproof CD player with 45 sec ESP⁴



Standard product information

Amplifier/ system

- Output power (in-ear headphone)
2 x 2.3mW RMS
- 1-Bit D/A converter for pure sound reproduction
- Dynamic bass boost
- Rotary volume control
- S/N ratio (A weighted) >100 dB
- Frequency response 20 Hz - 20 kHz
- Acoustic feedback

CD player

- 30-Track programmable, shuffle, repeat 1/all and introscan
- Search forward/ backward with sound
- Resume and hold

ESP⁴ - Fourth generation electronic skip protection

- Electronic skip protection with 45 second memory

LCD display

- Indications for track, time, 2-stage DBB, CD functions and battery status

Connections

- Headphone/line out Stereo, 3.5 mm
- DC in 4.0 mm, 4.5V, centre '+'

Power supply

- Batteries 2 x 1.5V, type AA/LR6/UM3 cell
- Battery playing time 22 hours (ESP on, Alkaline)/ 11 hours (Ni-MH)
- Built-in battery recharge function for ECO-PLUS NiMH batteries
- Automatic power switch-off

General

- Material High temperature resistant plastic
- Weight 214 g (excluding batteries)
- Product dimensions (mm) 135 L x 125 W x 30 H
- D-box dimensions /00 (mm) 245 L x 140 W x 49 H
- D-box dimensions /05 /11 /13 (mm) 245 L x 140 W x 54 H
- Master carton dimensions /00 (mm) 304 L x 253 W x 156 H
- Master carton dimensions /05 /11 /13 (mm) 334 L x 253 W x 156 H
- Master carton quantity 6

Accessories

- AC/DC adapter
- Stereo in-ear headphone
- Belt-clip
- ECO-PLUS Ni-MH rechargeable batteries

Jogproof

Fourth generation electronic skip protection for continuous music play with 45 second music buffer and upto five times faster shock recovery than conventional systems.

22-Hour playback (ESP on, 2 x AA Alkaline batteries)

Powersaving technology extends battery playing time to 22 hours with two regular LR6-size (AA) alkaline batteries.

Built-in recharge capability

Built-in recharge capability for ECO-PLUS Ni-MH batteries (batteries AY3362 included)

Digital dynamic bass boost (2-step)

Enhances bass at low, mid and high volume, to give deep, rich sounds.

CD-Rewritable compatible

Ensures that both CD-Recordable and CD-Rewritable discs, made by any CD-Recorder, can be played.

All CD program modes

Let you enjoy various CD program modes (repeat one/ repeat all / shuffle/ repeat shuffle/ introscan).

Heat resistant body

Unique composite material enables the CD player to withstand very high temperature.

ECO-PLUS Ni-MH rechargeable battery

Durable and environmental friendly rechargeable battery type which is quick and easy to charge.

1-Bit D/A converter

Advanced digital conversion technology ensures crystal-clear sound.

Hold

Locks all buttons to prevent interruption of play or change of program settings.

Resume

Bookmark function that ensures the CD starts precisely from the point it was stopped.

Automatic power off

Automatically switches off the CD player at the end of a compact disc.

CD next/ previous

Plays the next or previous track at the touch of a button.

CD music search

Searches the CD at high speed while still producing low-volume sound so you know exactly when to stop.

Repeat one/ all

Repeat the current track or the total CD.

Shuffle

Plays disc selection randomly, giving you each time a new sequence of tracks.

30-track programmable

Stores up to 30 of your favourite tracks for playing back in your order of preference.

Acoustic feedback

Confirms any key-push with friendly beep to acknowledge that a command has been given.

Printed in Hong Kong 2000-12-01
Specifications subject to modification
without notice

© 2000 Koninklijke Philips Electronics N.V.
All rights reserved

<http://www.philips.com>

Let's make things better.



PHILIPS