

Jogproof CD player with 45 sec ESP<sup>4</sup>



# Jogproof

- 22-Hours playback (ESP on, 2 x AA Alkaline batteries)
- Digital Dynamic Bass Boost
- CD-Rewritable compatible
- All CD play modes
- Headphone included



Let's make things better.



PHILIPS



# Jogproof CD player with 45 sec ESP<sup>4</sup>

## Standard product information

### Amplifier/ system

- Output power (in-ear headphone)  
2 x 6mW RMS
- 1-Bit D/A converter for pure sound reproduction
- Dynamic bass boost
- Rotary volume control
- S/N ratio  
(A weighted) >100 dB
- Frequency response 20 Hz - 20 kHz
- Acoustic feedback

### CD player

- 30-Track programmable, shuffle, repeat 1/all and introscan
- Search forward/backward with sound
- Resume
- Hold

### ESP - Electronic skip protection

- Electronic skip protection with 45 second memory

### LCD display

- Indications for track, time, Bass, CD functions and battery status

### Connections

- Headphone/line out Stereo, .14"
- DC in .16", 4.5V, center '+'

### Power supply

- Batteries 2 x 1.5V, type AA cell
- Battery playing time 22 hours (ESP on, Alkaline batteries)
- Automatic power switch-off

### General

- Material High temperature resistant plastic
- Weight .44 lbs
- Product dimensions 1.1" L x 5.44" W x 5.04" H
- Clamshell dimensions 3.2" L x 9.6" W x 9.6" H
- Clamshell weight 1.54 lbs
- Mastercarton dimensions 9.8" L x 12.8" W x 11.2" H
- Mastercarton weight 4.74 lbs
- Mastercarton quantity 3
- Country of Origin China
- Warranty 12 Months OTC Exchange

### Accessories

- Stereo headband headphone

### Jogproof

Fourth generation Electronic Skip Protection for continuous music play with 45 second music buffer and upto five times faster shock recovery than conventional systems.

### 22-Hours playback (ESP on, 2 x AA Alkaline batteries)

Powersaving technology extends battery playing time to 22 hours with two regular AA-size alkaline batteries.

### Digital Dynamic Bass Boost

Enhances bass at low, mid and high volume, to give deep, rich sounds.

### CD-Rewritable compatible

Ensures that both CD-Recordable and CD-Rewritable disks, made by any CD-Recorder, can be played.

### All CD play modes

Let's you enjoy various CD program modes (repeat one/ repeat all/ shuffle/ repeat shuffle/ introscan).

### Headphone included

### Heat resistant body

Unique composite material enables the CD player to withstand very high temperatures.

### 1-Bit D/A converter

Advanced digital conversion technology ensures crystal-clear sound.

### Hold

Locks all buttons to prevent interruption of play or change of program settings.

### Resume

Bookmark function that ensures the CD starts precisely from the point it was stopped.

### Automatic power off

Automatically switches off the CD player at the end of a compact disc.

### CD next/ previous

Plays the next or previous track at the touch of a button.

### CD music search

Searches the CD at high speed while still producing low-volume sound so you know exactly when to stop.

### Repeat one/ all

Repeat the current track or the total CD.

### Shuffle

Plays disc selection randomly, giving you each time a new sequence of tracks.

### 30-track programmable

Stores up to 30 of your favorite tracks for playing back in your order of preference.

### Acoustic feedback

Confirms any key-push with friendly beep to acknowledge that a command has been given.

UPC: 0 37849 90582 1

Master pack UPC: 1 37849 90582 8

Printed in Hong Kong 2000-12-01

Specifications subject to modification without notice

© 2000 Koninklijke Philips Electronics N.V.

All rights reserved

<http://www.philipsusa.com>

Let's make things better.



PHILIPS