



In-car CD player with 45 sec ESP<sup>4</sup>

# *Continuous* **In-car music**

- Jogproof
- 22-Hours playback (ESP on, 2 x AA Alkaline batteries)
- Digital Dynamic Bass Boost
- CD-Rewritable compatible
- All CD play modes
- Heat resistant body
- Headphone, belt-clip, car-kit and AC/DC adapter included



Let's make things better.



**PHILIPS**



# In-car CD player with 45 sec ESP<sup>4</sup>

## Standard product information

### Amplifier/ system

- Output power (in-ear headphone)  
2 x 3mW RMS
- 1-Bit D/A converter for pure sound reproduction
- Dynamic bass boost
- Rotary volume control
- S/N ratio  
(A weighted) >100 dB
- Frequency response 20 Hz - 20 kHz
- Acoustic feedback

### CD player

- 30-Track programmable, shuffle, repeat 1/all and introscan
- Search forward/backward with sound
- Resume
- Hold

### ESP - Electronic skip protection

- Electronic skip protection with 45 second memory

### LCD display

- Indications for track, time, Bass, CD functions and battery status

### Connections

- Headphone/line out Stereo, .14"
- DC in .16", 4.5V, center '+'

### Power supply

- Batteries 2 x 1.5V, type AA cell
- Battery playing time 22 hours (ESP on, Alkaline batteries)
- Automatic power switch-off

### General

- Material High temperature resistant plastic
- Weight .44 lbs (excluding batteries)
- Product dimensions 1.1"L x 5.44" W x 5.04" H
- Clamshell dimensions 3.94" L x 13.6" W x 11.03" H
- Clamshell weight 2 lbs
- Mastercarton dimensions 11.03" L x 14.7" W x 12.4" H
- Mastercarton weight 7.5 lbs
- Mastercarton quantity 3
- Country of Origin China
- Warranty 12 Months OTC Exchange

### Accessories

- AC/DC adapter
- Stereo headband headphone
- Belt-clip
- Car cassette adapter
- 4.5V Car cigarette lighter DC/DC adapter

### Logproof / continuous in-car music

Fourth generation Electronic Skip Protection for continuous music play with 45 second music buffer and upto five times faster shock recovery than conventional systems.

### 22-Hours playback (ESP on, 2 x AA Alkaline batteries)

Powersaving technology extends battery playing time to 22 hours with two regular AA-size alkaline batteries.

### Digital Dynamic Bass Boost

Enhances bass at low, mid and high volume, to give deep, rich sounds.

### CD-Rewritable compatible

Ensures that both CD-Recordable and CD-Rewritable disks, made by any CD-Recorder, can be played.

### All CD play modes

Let's you enjoy various CD program modes (repeat one/ repeat all/ shuffle/ repeat shuffle/ introscan).

### Heat resistant body

Unique composite material enables the CD player to withstand very high temperatures.

### Headphone, car-kit and AC/DC adapter included

### 1-Bit D/A converter

Advanced digital conversion technology ensures crystal-clear sound.

### Hold

Locks all buttons to prevent interruption of play or change of program settings.

### Resume

Bookmark function that ensures the CD starts precisely from the point it was stopped.

### Automatic power off

Automatically switches off the CD player at the end of a compact disc.

### CD next/ previous

Plays the next or previous track at the touch of a button

### CD music search

Searches the CD at high speed while still producing low-volume sound so you know exactly when to stop.

### Repeat one/ all

Repeat the current track or the total CD.

### Shuffle

Plays disc selection randomly, giving you each time a new sequence of tracks.

### 30-track programmable

Stores up to 30 of your favorite tracks for playing back in your order of preference.

### Acoustic feedback

Confirms any key-push with friendly beep to acknowledge that a command has been given.

UPC: 0 37849 90587 6

Master pack UPC: 1 37849 90587 3

Printed in Hong Kong 2000-12-01  
Specifications subject to modification without notice  
© 2000 Koninklijke Philips Electronics N.V.  
All rights reserved

<http://www.philipsusa.com>

Let's make things better.



PHILIPS