




In-car CD player with 45 sec ESP⁴

Continuous **In-car music**

- Jogproof
- 22-Hours playback (ESP on, 2 x AA Alkaline batteries)
- Digital Dynamic Bass Boost
- CD-Rewritable compatible
- All CD play modes
- Heat resistant body
- Headphone, belt-clip, car-kit and AC/DC adapter included



Let's make things better.



PHILIPS



In-car CD player with 45 sec ESP⁴

Standard product information

Amplifier/ system

- Output power (in-ear headphone)
2 x 6mW RMS
- 1-Bit D/A converter for pure sound reproduction
- Dynamic bass boost
- Rotary volume control
- S/N ratio
(A weighted) >100 dB
- Frequency response 20 Hz - 20 kHz
- Acoustic feedback

CD player

- 30-Track programmable, shuffle, repeat 1/all and introscan
- Search forward/backward with sound
- Resume
- Hold

ESP - Electronic skip protection

- Electronic skip protection with 45 second memory

LCD display

- Indications for track, time, Bass, CD functions and battery status

Connections

- Headphone/line out Stereo, .14"
- DC in .16", 4.5V, center '+'

Power supply

- Batteries 2 x 1.5V, type AA cell
- Battery playing time 22 hours (ESP on, Alkaline batteries)
- Automatic power switch-off

General

- Material High temperature resistant plastic
- Weight .44 lbs (excluding batteries)
- Product dimensions 1.1" L x 5.44" W x 5.04" H
- Clamshell dimensions 3.94" L x 13.6" W x 11.03" H
- Clamshell weight 2 lbs
- Mastercarton dimensions 11.03" L x 14.7" W x 12.4" H
- Mastercarton weight 7.5 lbs
- Mastercarton quantity 3
- Country of Origin China
- Warranty 12 Months OTC Exchange

Accessories

- AC/DC adapter
- Stereo headband headphone
- Belt-clip
- Car cassette adapter
- 4.5V Car cigarette lighter DC/DC adapter

Logproof / continuous in-car music

Fourth generation Electronic Skip Protection for continuous music play with 45 second music buffer and upto five times faster shock recovery than conventional systems.

22-Hours playback (ESP on, 2 x AA Alkaline batteries)

Powersaving technology extends battery playing time to 22 hours with two regular AA-size alkaline batteries.

Digital Dynamic Bass Boost

Enhances bass at low, mid and high volume, to give deep, rich sounds.

CD-Rewritable compatible

Ensures that both CD-Recordable and CD-Rewritable disks, made by any CD-Recorder, can be played.

All CD play modes

Let's you enjoy various CD program modes (repeat one/ repeat all/ shuffle/ repeat shuffle/ introscan).

Heat resistant body

Unique composite material enables the CD player to withstand very high temperatures.

Headphone, car-kit and AC/DC adapter included

1-Bit D/A converter

Advanced digital conversion technology ensures crystal-clear sound.

Hold

Locks all buttons to prevent interruption of play or change of program settings.

Resume

Bookmark function that ensures the CD starts precisely from the point it was stopped.

Automatic power off

Automatically switches off the CD player at the end of a compact disc.

CD next/ previous

Plays the next or previous track at the touch of a button.

CD music search

Searches the CD at high speed while still producing low-volume sound so you know exactly when to stop.

Repeat one/ all

Repeat the current track or the total CD.

Shuffle

Plays disc selection randomly, giving you each time a new sequence of tracks.

30-track programmable

Stores up to 30 of your favorite tracks for playing back in your order of preference.

Acoustic feedback

Confirms any key-push with friendly beep to acknowledge that a command has been given.

UPC: 0 37849 90601 9

Master pack UPC: 1 37849 90601 6

Printed in Hong Kong 2000-12-01
Specifications subject to modification without notice
© 2000 Koninklijke Philips Electronics N.V.
All rights reserved

<http://www.philipsusa.com>

Let's make things better.



PHILIPS