

**Accessory List**

| Type Number | AC/DC Adapter | Headphone     | Pouch | Battery | Car Cassette Adapter | Car DC/DC Adapter | Belt Clip | Remote |
|-------------|---------------|---------------|-------|---------|----------------------|-------------------|-----------|--------|
| AX5119      | --            | SBC HL351/77s | --    | --      | --                   | --                | yes       | AY3768 |

**\*Refer to the following pages for Product Specification**

**Accessory List**

| Type Number | AC/DC Adapter | Headphone     | Pouch | Battery | Car Cassette Adapter | Car DC/DC Adapter | Belt Clip | Remote |
|-------------|---------------|---------------|-------|---------|----------------------|-------------------|-----------|--------|
| AX5111      |               | SBC HL351/77  |       |         |                      |                   | Yes       |        |
| AX5112      |               | SBC HL351/77  |       |         |                      |                   | Yes       |        |
| AX5113      |               | SBC HL351/77  |       |         |                      |                   | Yes       |        |
| AX5114      |               | SBC HL351/77  |       |         |                      |                   | Yes       |        |
| AX5115      |               | SBC HL351/77  |       |         | AY3501               | AY3545<br>AY3548  | Yes       |        |
| AX5116      |               | SBC HL351/77  |       |         | AY3501               | AY3545<br>AY3548  | Yes       |        |
| AX5117      |               | SBC HL351/77  |       |         | AY3501               | AY3545<br>AY3548  | Yes       |        |
| AX5118      |               | SBC HL351/77s |       |         | AY3501               | AY3545<br>AY3548  | Yes       | AY3768 |

**\*Refer to the following pages for Product Specification**

45-second ESP CD player

# Jogproof

- 45-second Electronic skip protection
- 25-hour playback (2 x AA Alkaline batteries)
- Digital dynamic bass boost
- CD-Rewritable compatible
- All CD program modes



Let's make things better.



PHILIPS



# 45-second ESP CD player

## Standard product information

### Amplifier/ system

- Output power (in-ear headphone)  
2 x 4mW RMS
- 1-Bit D/A convertor for pure sound reproduction
- Dynamic bass boost
- Rotary volume control
- S/N ratio (A weighted) >85 dB
- Frequency response 20 Hz - 20 kHz
- Audible feedback

### CD player

- 30-track programmable, shuffle, repeat one/all and introscan
- Search forward/ backward with sound
- Resume and hold

### Electronic skip protection

- Electronic skip protection with 45 second memory

### LCD display

- Indications for track, time, ESP, DBB, CD functions and battery status

### Connections

- Headphone/line out stereo, 3.5 mm
- DC in 4.0 mm, 4.5V, centre '+'

### Power supply

- Batteries 2 x 1.5V, type AA/LR6/UM3 cell
- Battery playing time 25 hours (Alkaline batteries)
- Automatic power switch-off

### General

- Material High temperature resistant plastic
- Weight 214 g (excluding batteries)
- Product dimensions (mm) 135 L x 125 W x 30 H
- D-box dimensions /00c (mm) 245 L x 140 W x 49 H
- Master carton dimensions /00c (mm) 304 L x 253 W x 156 H
- Master carton quantity 6

### Accessories

- AC/DC adapter
- Stereo in-ear headphone
- Belt-clip

### 45-second Electronic skip protection

Electronic skip protection detects shocks automatically and allows music play continuously with 45-second music buffer.

### 25-hour playback (2 x AA Alkaline batteries)

Powersaving technology extends battery playing time to 25 hours with two regular LR6-size (AA) alkaline batteries.

### Digital dynamic bass boost

Enhances bass at low, mid and high volume, to give deep, rich sounds.

### CD-Rewritable compatible

Ensures that both CD-Recordable and CD-Rewritable discs, made by any CD-Recorder, can be played.

### All CD program modes

Let you enjoy various CD program modes (repeat one/ repeat all/ shuffle/ repeat shuffle/ introscan).

### Heat resistant body

Unique composite material enables the CD player to withstand very high temperature.

### 1-Bit D/A converter

Advanced digital conversion technology ensures crystal-clear sound.

### Hold

Locks all buttons to prevent interruption of play or change of program settings.

### Resume

Bookmark function that ensures the CD starts precisely from the point it was stopped.

### Automatic power off

Automatically switches off the CD player at the end of a compact disc.

### CD next / previous

Plays the next or previous track at the touch of a button.

### CD music search

Searches the CD at high speed while still producing low-volume sound so you know exactly when to stop.

### Repeat one/ all

Repeat the current track or the total CD.

### Shuffle

Plays disc selection randomly, giving you each time a new sequence of tracks.

### 30-track programmable

Stores up to 30 of your favourite tracks for playing back in your order of preference.

### Audible feedback

Confirms any key-push with friendly beep to acknowledge that a command has been given.

Printed in Hong Kong 2001-11-12  
Specifications subject to modification without notice  
© 2001 Koninklijke Philips Electronics N.V.  
All rights reserved

[www.philips.com](http://www.philips.com)  
[www.audio.philips.com](http://www.audio.philips.com)

Let's make things better.



PHILIPS