

Accessory List

Type Number	AC/DC Adapter	Headphone	Pouch	Battery	Car Cassette Adapter	Car DC/DC Adapter	Belt Clip	Remote
AX5210	--	SBC HS383/77	--	--	--	--	--	--
AX5211	--	SBC HS383/77	--	--	--	--	--	--
AX5212	--	SBC HS383/77	--	--	--	--	--	--
AX5215	--	SBC HS383/77s	--	--	AY3501/00	AY3545/17 AY3548/17	--	AY3778
AX5219	--	SBC HS383/77s	AY3273	--	--	--	--	AY3778

***Refer to the following pages for Product Specification**

Portable CD player

AX 5200

Compact + slim urban action gear

Jogproof

- 45-second Electronic skip protection

Unique

- Round, compact and slim design

Ease of control

- Wearable remote control supplied

Extra long battery playing time

- 30-hour playback (2 x AA Alkaline batteries)

Playback all kinds of discs

- Plays CD, CDR and CDRW discs



PHILIPS

Portable CD player



Standard product information

Amplifier/ system

- Output power (in-ear headphone)
2 x 5mW RMS
- 1-Bit D/A converter for pure sound reproduction
- Dynamic bass boost
- Digital volume control
- S/N ratio (A weighted) >84 dB
- Frequency response 20 Hz - 20 kHz
- Audible feedback

CD player

- 30-Track programmable, shuffle, repeat one/ all and introscan
- Search forward/ backward with sound
- Resume and hold

Electronic skip protection

- Electronic skip protection with 45 second memory

LCD display

- Indications for track, time, ESP, DBB, CD functions and battery status

Connections

- Headphone/ line out stereo, 3.5 mm
- DC in 4.0 mm, 4.5V, centre '+'

Power supply

- Batteries 2 x 1.5V, type AA/LR6/UM3 cell
- Battery playing time 30 hours (2 x AA alkaline batteries)
- Battery playing time 12 hours (2 x AAA alkaline batteries)
- Automatic power switch-off

General

- Material High temperature resistant plastic
- Weight 170 g (excluding batteries)
- Product dimensions 137 D x 137 W x 21 H (mm)
- D-box dimensions 165 D x 148 W /00c (mm) x 49 H
- Master carton 306 D x 174 W dimensions /00c (mm) x 166 H
- Master carton quantity 6

Accessories

- Stereo in-ear headphone
- In-cord 4-key remote control

45-second Electronic skip protection

Electronic skip protection detects shocks automatically and allows music play continuously with 45-second music buffer.

30-hour playback (2 x AA Alkaline batteries)

Powersaving technology extends battery playing time to 30 hours with two regular LR6-size (AA) alkaline batteries.

Digital dynamic bass boost

Enhances bass at low, mid and high volume, to give deep, rich sounds.

Plays CD, CDR and CDRW discs

Ensures that both CD-Recordable and CD-Rewritable discs, made by any CD-Recorder, can be played.

All CD program modes

Let you enjoy various CD program modes (repeat one/ repeat all/ shuffle/ repeat shuffle/ introscan).

Heat resistant body

Unique composite material enables the CD player to withstand very high temperature.

1-Bit D/A converter

Advanced digital conversion technology ensures crystal-clear sound.

Hold

Locks all buttons to prevent interruption of play or change of program settings.

Resume

Bookmark function that ensures the CD starts precisely from the point it was stopped.

Automatic power off

Automatically switches off the CD player at the end of a compact disc.

CD next/ previous

Plays the next or previous track at the touch of a button.

CD music search

Searches the CD at high speed while still producing low-volume sound so you know exactly when to stop.

Repeat one/ all

Repeat the current track or the total CD.

Shuffle

Plays disc selection randomly, giving you each time a new sequence of tracks.

30-track programmable

Stores up to 30 of your favourite tracks for playing back in your order of preference.

Audible feedback

Confirms any key-push with friendly beep to acknowledge that a command has been given.

Printed in Hong Kong 2002-09-18
Specifications subject to modification
without notice
2002 © Koninklijke Philips Electronics N.V.
All rights reserved

www.philips.com
www.audio.philips.com

