

CD Sound machine

- **Dynamic bass boost**

Enhances bass tone frequencies to give deep, rich sounds.

- **20-track programmable**

Stores up to 20 of your favourite CD tracks for playing back in your order of preference.

- **Shuffle play**

Plays disc selection randomly, giving you a new sequence of tracks each time.

- **Repeat one/ all**

Repeats the current track, the total CD, or your pre-selected programme.

- **CD synchro start recording**

Synchronises the start of a recording on audio cassette with the start of a CD at the touch of a button.



Standard product information**Compact disc player**

- Top loader
- 20 Track CD programme
- Shuffle and repeat function
- CD next/previous track search
- CD music search
- CD synchro start recording

Cassette deck

- Single stereo cassette deck
- Normal tape type
- Full auto stop
- Automatic recording level control

Tuner

- Analogue tuning
- Wavebands
 - /00, /05 : FM stereo/MW/LW
 - /01, /11 : FM stereo/MW
 - /17 : FM stereo/AM
 - /14 : FM1/FM2/MW/LW
- Frequency ranges
 - FM 87.5 - 108 Mhz
 - FM 65.8 - 74/87.5 - 108 Mhz (/14)
 - AM 530 - 1710 kHz (/17)
 - MW 525 - 1607 kHz
 - LW 148.5 - 284 kHz
- Telescopic aerial for FM reception
- Ferroceptor for AM reception

Display

- Large LCD display

Sound system

- Output power : 2 x 1.0 W RMS
- Dynamic bass boost
- 2 x 4" Speakers
- Metal speaker grilles
- Rotary volume control

Power supply

- AC/DC Operation
- Batteries : 6 x 1.5V, R20 cells

Connections

- Stereo headphones : 3.5 mm

General

- Dimensions product : 400 mm W x 166 mm H x 235 mm D
- Packaging dimensions : 470 mm W x 211 mm H x 260 mm D
- Weight of product : 2.8 kg
- Weight including packaging : 3.5 kg

Power supplies

- /00, /05, /14 : 230V, 50Hz
- /17 : 120 V, 60 Hz
- /01, /11 : 120/230 V, 50 Hz

Product highlights**Compact disc digital audio player**

Compact Disc technology that combines superb digital sound quality with the convenience of random track access and CD functions like CD programme, Shuffle Play and Repeat.

Analogue tuner

High-quality tuner with sensitive operation for maximum tuning control.

Ferroceptor AM antenna

Built-in ferrite bar antenna for excellent AM reception.

Telescopic FM antenna

Extendible FM antenna for excellent FM reception.

Stereo cassette deck

Play back recorded tapes on this full-functional stereo cassette deck, and record from the built-in CD player or tuner.

4" Full-range speakers

For excellent sound performance across the entire audio frequency spectrum.

AC/DC operation

Operates either on batteries or mains supply, using the detachable AC power cord.

Metal mesh speaker grilles

Perforated, anodized grilles protect the speaker components.

Stereo headphone socket

Enables stereo headphones to be used for private listening pleasure. Automatically switches off speakers when used.

Two-digit LCD display

Displays CD track numbers and play modes like Shuffle, Repeat, and CD programme.