

CD Sound Machine



# **Bass** *reflex speaker system*

- Dynamic bass boost
- 19-track programmable
- Repeat one/ all
- CD synchro start recording



*Let's make things better.*



**PHILIPS**

# CD Sound Machine



## Standard product information

### Compact disc player

- Top loader
- 19 Track CD programme
- Repeat function
- CD next/previous track search
- CD music search
- CD synchro start recording

### Cassette deck

- Single stereo cassette deck
- Normal tape type
- Full auto stop
- Automatic recording level control

### Tuner

- Analogue tuning
- Wavebands /17 FM stereo/AM
- Frequency ranges FM 87.5 - 108 Mhz  
AM 530 - 1710 kHz  
(/17)
- Telescopic aerial for FM reception
- Ferroceptor for AM reception

### Display

- 2 digit LCD display

### Sound system

- Output power 2 x 1.0 W RMS

### Dynamic bass boost

- 2 x 4" Speakers
- Metal speaker grilles
- Front rotary volume control

### Power supply

- AC/DC Operation
- Batteries 6 x 1.5V, R14 cells

### General

- Dimensions product 400 mm W x 173 mm H  
x 240 mm D
- Packaging dimensions 470 mm W x 211 mm H  
x 260 mm D
- Weight of product 2.75 kg
- Weight including packaging 3.5 kg

### Power supplies

- /00, /05, /14 230V, 50Hz
- /17 120V, 60 Hz
- /01, /11, /16 120/230V, 50 Hz

### Bass reflex speaker system

Acoustic system that enhances the upper bass tones to provide a warmer, punchier bass sound.

### Dynamic bass boost

Enhances bass tone frequencies to give deep, rich sounds.

### 19-track programmable

Stores up to 20 of your favourite CD tracks for playing back in your order of preference.

### Repeat one/ all

Repeats the current track, the total CD, or your pre-selected programme.

### CD synchro start recording

Synchronises the start of a recording on audio cassette with the start of a CD at the touch of a button.

### Analogue tuner

### Ferroceptor AM antenna

Built-in ferrite bar antenna for excellent AM reception.

### Telescopic FM antenna

Extendible FM antenna for excellent FM reception.

### Stereo cassette deck

Play back recorded tapes on this full-functional stereo cassette deck, and record from the built-in CD player or tuner.

### 4" Full-range speakers

For excellent sound performance across the entire audio frequency spectrum.

### AC/DC operation

Operates either on batteries or mains supply, using the detachable AC power cord.

### Metal mesh speaker grilles

Perforated, anodized grilles protect the speaker components.

### Two-digit LCD display

Displays CD track numbers and play modes like Repeat, and CD programme.

Printed in Hong Kong 2000-12-01  
Specifications subject to modification  
without notice

© 2000 Koninklijke Philips Electronics N.V.  
All rights reserved

<http://www.philips.com>

Let's make things better.



PHILIPS